

Z1K-336-11Z Cut Sheet



Schmersal IEC limit switch, one-way horizontal lever with plastic roller, 90-degree adjustable head, (1) N.O./ (1) N.C. contact(s), snap action, 30mm hole spacing, glass-fiber thermoplastic, (1) M20 x 1.5 entry with 1/2in NPT adapter.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/Z1K-336-11Z>

Technical Specifications

Brand	Schmersal
Item	Limit switch
Switch Type	IEC
Actuator Type	One-way horizontal lever with plastic roller
Head Type	90-degree adjustable
Contact Type	(1) N.O./ (1) N.C.
Action	Snap action
Reset	No
Body Width	40.5mm
Mounting Hole Spacing	30mm
Material	Glass-fiber thermoplastic
IP Rating	IP67
Operating Temperature	-30 to 80 deg C
Connection	(1) M20 x 1.5 entry with 1/2in NPT adapter

Agency Approvals

UL Listed File #	E57648
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/Z1K-336-11Z.pdf>
See store item page for other formats.