



Klemsan triggered delay relay timer, 0.1 seconds to 99.9 hours selectable timing range, 12–240 VAC/VDC operating voltage, 10A contact rating, (1) SPDT timed relay output(s), 35mm DIN rail mount, screw terminal(s).

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/Z1K-M2A>

Technical Specifications

Brand	Klemsan
Item	Relay timer
Timer Type	Triggered delay
Indicator	LED
Timing Range	0.1 seconds to 99.9 hours selectable
Operating Voltage	12–240 VAC/VDC
Timer Output Type(s)	(1) SPDT timed relay
Output Type	(1) N.O., (1) N.C.
Timer Function(s)	<ul style="list-style-type: none">triggered on-delaytriggered off-delay
Contact Rating	10A
Mounting	35mm DIN rail
Connector Type	Screw terminal(s)

Agency Approvals

UL Listed File #	E361956
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
[https://cdn.automationdirect.com
/static/drawings/2d/Z1K-M2A.pdf](https://cdn.automationdirect.com/static/drawings/2d/Z1K-M2A.pdf)
See store item page for other formats.