



Klemsan multi-mode delay relay timer, 0.1 seconds to 99.9 hours selectable timing range, 12-240 VAC/VDC operating voltage, 10A contact rating, (1) SPDT timed relay output(s), 35mm DIN rail mount, screw terminal(s).

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/Z1T-M2>

## Technical Specifications

<b>Brand</b>	Klemsan
<b>Item</b>	Relay timer
<b>Timer Type</b>	Multi-mode delay
<b>Indicator</b>	LED
<b>Timing Range</b>	0.1 seconds to 99.9 hours selectable
<b>Operating Voltage</b>	12-240 VAC/VDC
<b>Timer Output Type(s)</b>	(1) SPDT timed relay
<b>Output Type</b>	(1) N.O., (1) N.C.
<b>Timer Function(s)</b>	• on-delay • off-delay
<b>Contact Rating</b>	10A
<b>Mounting</b>	35mm DIN rail
<b>Connector Type</b>	Screw terminal(s)

## Agency Approvals

<b>UL Listed File #</b>	E361956
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
[https://cdn.automationdirect.com  
/static/drawings/2d/Z1T-M2.pdf](https://cdn.automationdirect.com/static/drawings/2d/Z1T-M2.pdf)  
See store item page for other formats.