

Z4R-235-11Z Cut Sheet



Schmersal IEC limit switch, metal plunger with plastic roller with fixing nuts, 90-degree adjustable head, (1) N.O./ (1) N.C. contact(s), snap action, 20-22mm hole spacing, zinc alloy, M20 x 1.5 entry with 1/2in NPT adapter.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/Z4R-235-11Z>

Technical Specifications

Brand	Schmersal
Item	Limit switch
Switch Type	IEC
Actuator Type	Metal plunger with plastic roller with fixing nuts
Head Type	90-degree adjustable
Contact Type	(1) N.O./ (1) N.C.
Action	Snap action
Reset	No
Body Width	30mm
Mounting Hole Spacing	20-22mm
Material	Zinc alloy
IP Rating	IP67
Operating Temperature	-30 to 80 deg C
Connection	M20 x 1.5 entry with 1/2in NPT adapter

Agency Approvals

UL Listed File #	E57648
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document