

# Z4VH-335-02Z Cut Sheet



Schmersal IEC limit switch, side rotary lever with plastic roller, 90-degree adjustable head, (2) N.C. contact(s), snap action, 30mm hole spacing, aluminum, (1) M20 x 1.5 entry with 1/2in NPT adapter.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/Z4VH-335-02Z>

## Technical Specifications

Brand	Schmersal
Item	Limit switch
Switch Type	IEC
Actuator Type	Side rotary lever with plastic roller
Head Type	90-degree adjustable
Contact Type	(2) N.C.
Action	Snap action
Reset	No
Body Width	40.5mm
Mounting Hole Spacing	30mm
Material	Aluminum
IP Rating	IP67
Operating Temperature	-30 to 80 deg C
Connection	(1) M20 x 1.5 entry with 1/2in NPT adapter

## Agency Approvals

UL Listed File #	E57648
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/Z4VH-335-02Z.pdf>  
See store item page for other formats.