

# ZL-D24-CBL40-1P Cut Sheet



ZIPLink PLC I/O cable, 40-pin connector to pigtail, 180-degree connector angle, 3.2ft/1m cable length. For use with BRX modules and DirectLOGIC DL205 and DL405 modules.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ZL-D24-CBL40-1P>

## Technical Specifications

<b>Brand</b>	ZIPLink
<b>Item</b>	Cable
<b>Cable Type</b>	PLC I/O
<b>Device Connection</b>	40-pin connector
<b>ZIPLink Connection</b>	Pigtail
<b>Connector Angle</b>	180-degree
<b>Shielded</b>	No
<b>Twisted Pair</b>	No
<b>Cable Length</b>	3.2ft/1m
<b>Conductor Size</b>	24 AWG
<b>For Use With</b>	BRX modules and DirectLOGIC DL205 and DL405 modules

## Agency Approvals

<b>UL Listed File #</b>	E200031
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>