

ZL-D24-CBL40-2 Cut Sheet

ZIPLink PLC I/O cable, 40-pin connector to 40-pin connector, 180-degree connector angle, 6.5ft/2m cable length. For use with BRX modules and DirectLOGIC DL205 and DL405 modules.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ZL-D24-CBL40-2>

Technical Specifications

Brand	ZIPLink
Item	Cable
Cable Type	PLC I/O
Device Connection	40-pin connector
ZIPLink Connection	40-pin connector
Connector Angle	180-degree
Shielded	No
Twisted Pair	No
Cable Length	6.5ft/2m
Conductor Size	24 AWG
For Use With	BRX modules and DirectLOGIC DL205 and DL405 modules

Agency Approvals

UL Listed File #	E200031
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/ZL-D24-CBL40-2.pdf>
See store item page for other formats.