

ZL-P1-CBL10-2 Cut Sheet



ZIPLink PLC I/O cable, 10-position terminal block to 24-pin connector, 90-degree connector angle, 6.5ft/2m cable length. For use with Productivity1000 modules.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ZL-P1-CBL10-2>

Technical Specifications

Brand	ZIPLink
Item	Cable
Cable Type	PLC I/O
Device Connection	10-position terminal block
ZIPLink Connection	24-pin connector
Connector Angle	90-degree
Shielded	No
Twisted Pair	No
Cable Length	6.5ft/2m
Conductor Size	24 AWG
For Use With	Productivity1000 modules

Agency Approvals

UL Listed File #	None
UL Recognized File #	E139594
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/ZL-P1-CBL10-2.pdf>
See store item page for other formats.