

ZP-JBH64-00-FW Cut Sheet



ZPport junction block, 6 ports, 5-pin M12 sockets, 4-wire, 150 VAC/VDC, 3A, field-wired connection, IP67. (2) port caps for unused ports included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ZP-JBH64-00-FW>

Technical Specifications

Brand	ZIPport
Item	Junction block
Number of Ports	6
Socket Type	5-pin M12
Wires Per Socket	4-wire
Socket Current	3A
I/O Per Socket	1
Voltage Rating	150 VAC/VDC
Number Of Commons	1
Load Current	8A/common
Connector Type	Field-wired connection
IP Rating	IP67
Includes	(2) port caps for unused ports

Agency Approvals

UL Listed File #	E328610
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document