

ZP-JBH64-2N-FW Cut Sheet



ZIPport junction block, 6 ports, 5-pin M12 sockets, 4-wire, 48 VDC, 3A, power and NPN LED indicator(s), field-wired connection, IP67. (2) port caps for unused ports included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ZP-JBH64-2N-FW>

Technical Specifications

| | |
|-------------------|--------------------------------|
| Brand | ZIPport |
| Item | Junction block |
| Number of Ports | 6 |
| Socket Type | 5-pin M12 |
| Wires Per Socket | 4-wire |
| Socket Current | 3A |
| I/O Per Socket | 1 |
| Voltage Rating | 48 VDC |
| Number Of Commons | 1 |
| Load Current | 8A/common |
| Indicator | Power and NPN LED |
| Connector Type | Field-wired connection |
| IP Rating | IP67 |
| Includes | (2) port caps for unused ports |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | E328610 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/ZP-JBH64-2N-FW.pdf>
See store item page for other formats.