

# ZP-MC-CG-11P5 Cut Sheet

ZIPport cable gland, PG11 thread type, polyamide, light gray, accepts 7 to 12mm diameter cable, IP66. (3) elastomer compression seals included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ZP-MC-CG-11P5>



## Technical Specifications

Brand	ZIPport
Item	Cable gland
Thread Type	PG11
Material	Polyamide
Color	Light gray
Cable OD Range	7 to 12mm
IP Rating	IP66
Strain Relief	No
Includes	(3) elastomer compression seals

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/ZP-MC-CG-11P5.pdf>  
See store item page for other formats.