

# ZP-MC-CG-29M5 Cut Sheet



ZIPport cable gland, PG29 thread type, nickel-plated brass, accepts 17.5 to 26.5mm diameter cable, IP66. (4) elastomer compression seals included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ZP-MC-CG-29M5>

---

## Technical Specifications

<b>Brand</b>	ZIPport
<b>Item</b>	Cable gland
<b>Thread Type</b>	PG29
<b>Material</b>	Nickel-plated brass
<b>Cable OD Range</b>	17.5 to 26.5mm
<b>IP Rating</b>	IP66
<b>Strain Relief</b>	No
<b>Includes</b>	(4) elastomer compression seals

---

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>