

ZP-MC-CG-29M5 Cut Sheet



ZIPport cable gland, PG29 thread type, nickel-plated brass, accepts 17.5 to 26.5mm diameter cable, IP66. (4) elastomer compression seals included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ZP-MC-CG-29M5>

Technical Specifications

Brand	ZIPport
Item	Cable gland
Thread Type	PG29
Material	Nickel-plated brass
Cable OD Range	17.5 to 26.5mm
IP Rating	IP66
Strain Relief	No
Includes	(4) elastomer compression seals

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/ZP-MC-CG-29M5.pdf>
See store item page for other formats.