

ZP-PGA-48-400 Cut Sheet



ZIPport panel interface connector, GFCI duplex 120 VAC outlet, (1) 9-pin D-sub connector with female exterior/male interior, (1) USB B port with female exterior/USB A female interior, (1) USB A port with female exterior/USB B female interior.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ZP-PGA-48-400>

Technical Specifications

Brand	ZIPport
Item	Connector
Connector Type	Panel interface
Power Outlet	GFCI duplex 120 VAC
Communication Port Type	(1) 9-pin D-sub connector with female exterior/ male interior, (1) USB B port with female exterior/USB A female interior, (1) USB A port with female exterior/USB B female interior
Circuit Breaker Type	3A circuit breaker
Connector Housing Size	48B
Housing Material	Heavy-duty die-cast aluminum
Lever Type	Single
Includes	Gasket

Agency Approvals

UL Listed File #	E495019
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/ZP-PGA-48-400.pdf>
See store item page for other formats.