


ZP-S1-5FP-6M Cut Sheet



ZPport connection cable, 7/8in - 16 UN2 thread nut 5-pin female axial to pigtail with North American color code, PVC outer jacket, yellow, nickel-plated brass connector, 19.6ft/6m cable length, IP67.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ZP-S1-5FP-6M>

Technical Specifications

Brand	ZIPport
Item	Cable
Cable Type	Connection
Connection 1	7/8in - 16 UN2 thread nut 5-pin female axial
Connection 2	Pigtail with North American color code
Jacket Material	PVC outer jacket
Jacket Color	Yellow
Connector Material	Nickel-plated brass
Shielded	No
Cable Length	19.6ft/6m
IP Rating	IP67

Agency Approvals

UL Listed File #	E328610
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document