

# ZP-S1C-4MR-0P3M-18 Cut Sheet



ZIPport bulkhead connector, 7/8in 4-pin male to pigtail, 18 AWG, 0.9ft/0.3m cable length, ether-based polyurethane conductor insulation material, IP67.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ZP-S1C-4MR-0P3M-18>

## Technical Specifications

Brand	ZIPport
Item	Connector
Form Factor	Bulkhead
Connection 1	7/8in male with male threads 4-wire/4-pin
Connection 2	Pigtail
Shielded	No
Cable Length	0.9ft/0.3m
Conductor Size	18 AWG
Conductor Insulation Material	Ether-based polyurethane
Housing Material	Anodized aluminum
IP Rating	IP67
Includes	Mounting nut(s)

## Agency Approvals

UL Listed File #	E328610
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/ZP-S1C-4MR-0P3M-18.pdf>  
See store item page for other formats.