

ZR-236-11Z Cut Sheet



Schmersal IEC limit switch, metal plunger with plastic roller, 90-degree adjustable head, (1) N.O./1) N.C. contact(s), snap action, 20-22mm hole spacing, glass-fiber thermoplastic, M20 x 1.5 entry with 1/2in NPT adapter.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ZR-236-11Z>

Technical Specifications

| | |
|------------------------------|----------------------------------------|
| Brand | Schmersal |
| Item | Limit switch |
| Switch Type | IEC |
| Actuator Type | Metal plunger with plastic roller |
| Head Type | 90-degree adjustable |
| Contact Type | (1) N.O./1) N.C. |
| Action | Snap action |
| Reset | No |
| Body Width | 30mm |
| Mounting Hole Spacing | 20-22mm |
| Material | Glass-fiber thermoplastic |
| IP Rating | IP67 |
| Operating Temperature | -30 to 80 deg C |
| Connection | M20 x 1.5 entry with 1/2in NPT adapter |

Agency Approvals

| | |
|-----------------------------|----------------------------------------|
| UL Listed File # | E57648 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |