

ZV7H-235-02Z Cut Sheet



Schmersal IEC limit switch, side rotary adjustable lever with plastic roller, 90-degree adjustable head, (2) N.C. contact(s), snap action, 20-22mm hole spacing, zinc alloy, M20 x 1.5 entry with 1/2in NPT adapter.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ZV7H-235-02Z>

Technical Specifications

Brand	Schmersal
Item	Limit switch
Switch Type	IEC
Actuator Type	Side rotary adjustable lever with plastic roller
Head Type	90-degree adjustable
Contact Type	(2) N.C.
Action	Snap action
Reset	No
Body Width	30mm
Mounting Hole Spacing	20-22mm
Material	Zinc alloy
IP Rating	IP67
Operating Temperature	-30 to 80 deg C
Connection	M20 x 1.5 entry with 1/2in NPT adapter

Agency Approvals

UL Listed File #	E57648
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/ZV7H-235-02Z.pdf>
See store item page for other formats.