

# ZV7H-235-11Z Cut Sheet



Schmersal IEC limit switch, side rotary adjustable lever with plastic roller, 90-degree adjustable head, (1) N.O./ (1) N.C. contact(s), snap action, 20-22mm hole spacing, zinc alloy, M20 x 1.5 entry with 1/2in NPT adapter.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ZV7H-235-11Z>

## Technical Specifications

|                              |                                                  |
|------------------------------|--------------------------------------------------|
| <b>Brand</b>                 | Schmersal                                        |
| <b>Item</b>                  | Limit switch                                     |
| <b>Switch Type</b>           | IEC                                              |
| <b>Actuator Type</b>         | Side rotary adjustable lever with plastic roller |
| <b>Head Type</b>             | 90-degree adjustable                             |
| <b>Contact Type</b>          | (1) N.O./ (1) N.C.                               |
| <b>Action</b>                | Snap action                                      |
| <b>Reset</b>                 | No                                               |
| <b>Body Width</b>            | 30mm                                             |
| <b>Mounting Hole Spacing</b> | 20-22mm                                          |
| <b>Material</b>              | Zinc alloy                                       |
| <b>IP Rating</b>             | IP67                                             |
| <b>Operating Temperature</b> | -30 to 80 deg C                                  |
| <b>Connection</b>            | M20 x 1.5 entry with 1/2in NPT adapter           |

## Agency Approvals

|                             |                                        |
|-----------------------------|----------------------------------------|
| <b>UL Listed File #</b>     | E57648                                 |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |