

Enclosure Accessories - Universal Deep-Hinged Window Door



Applications

The Wiegmann Universal Deep Hinged Door is styled after their N 412 Ultimate Series Enclosures. Doors are compatible with any NEMA 3R, 4, 4X, and 12 rated enclosures.

Deep-hinged window doors provide a degree of protection for HMIs or other operator interface devices that are installed on electrical enclosures. This allows for easy access to the devices with a hinged door and 1/4-turn latches. Viewing windows allow the operator to monitor the devices while the door is latched shut, keeping them protected during operation.



WADW131602



WADW131602SS

Construction

- Quarter-turn style latching for easy access.
- Latch type can be changed using [N41214 series latches](#) (sold separately).
- Concealed hinges with removable pins.
- Fabricated from 14 gauge carbon steel or 14 gauge 304 stainless steel.
- Carbon steel models have an ANSI 61 gray light-textured polyester powder finish. Stainless steel models have a No. 3 intermediate polished finish.
- Polycarbonate viewing window for clear visibility.
- Drill template and mounting hardware provided.
- Door and mounting surface are sealed with poured-in-place polyurethane gasket.

Listing

- UL Recognized type 3R, 4, 12, and 4X (SS only) [UL File E64791]
- IP66
- CSA Type 3R, 4, 12 and 4x (SS only) [CSA File 222873]

Enclosure Shipping Schedule					
Same day	1 - 5 days	1 - 7 days	1 - 10 days	1 - 15 days	1 - 20 days

Color indicates shipping lead time in business days.



Enclosure Accessories - Universal Deep-Hinged Window Door									
ANSI 61 Gray Steel	Price	304 Stainless Steel	Price	Height	Width	Depth	Window Height	Window Width	Wt. (lb)
WADW131602	\$435.00	WADW131602SS	\$851.00	12.75 [324]	15.88 [403]	2.75 [70]	8.68 [220]	9.83 [250]	11.0
WADW150902	\$457.00	WADW150902SS	\$888.00	14.75 [375]	9.5 [241]		10.68 [271]	3.41 [87]	8.0
WADW191302	\$518.00	WADW191302SS	\$1,102.00	18.75 [476]	13.5 [343]		14.68 [373]	7.41 [188]	14.0
WADW231302	\$588.00	WADW231302SS	\$1,176.00	22.75 [578]	13.5 [343]		18.68 [474]	7.41 [188]	17.0
WADW231702	\$629.00	WADW231702SS	\$1,251.00	22.75 [578]	17.5 [445]		18.68 [474]	11.41 [290]	21.0
WADW232602	\$750.00	WADW232602SS	\$1,567.00	22.75 [578]	26.25 [667]		18.68 [474]	20.22 [514]	32.0
WADW292002	\$750.00	WADW292002SS	\$1,567.00	28.75 [731]	20.25 [514]		24.68 [627]	14.22 [361]	31.0

Notes: Dimensions in inches [millimeters].
Cutout dimension: Height - 3.00 [76], Width - 3.00 [76]

