


# DINnectors<sup>®</sup> Accessories

## Terminal Plugs



**DN-xxPLUG / DN-xxPLUGMN**



Accessories – Terminal Plugs							
Plugs* Part Number	Pcs/Pkg	Price/Pkg	Plugs* Part Number	Pcs/Pkg	Price/Pkg	Number of Poles	Length mm [in]
<b>DN-2PLUG</b>	200	\$68.00	<b>DN-2PLUGMN</b>	10	\$4.25	2	10.2 [0.40]
<b>DN-3PLUG</b>	200	\$106.00	<b>DN-3PLUGMN</b>	10	\$6.50	3	15.2 [0.60]
<b>DN-4PLUG</b>	100	\$70.00	<b>DN-4PLUGMN</b>	10	\$8.50	4	20.3 [0.80]
<b>DN-5PLUG</b>	100	\$81.00	<b>DN-5PLUGMN</b>	10	\$10.50	5	25.4 [1.00]
<b>DN-6PLUG</b>	100	\$105.00	<b>DN-6PLUGMN</b>	10	\$10.50	6	30.5 [1.20]
<b>DN-7PLUG</b>	50	\$55.00	<b>DN-7PLUGMN</b>	5	\$8.50	7	35.6 [1.40]
<b>DN-8PLUG</b>	50	\$69.00	<b>DN-8PLUGMN</b>	5	\$8.50	8	40.6 [1.60]
<b>DN-9PLUG</b>	50	\$76.00	<b>DN-9PLUGMN</b>	5	\$9.25	9	45.7 [1.80]
<b>DN-10PLUG</b>	50	\$81.00	<b>DN-10PLUGMN</b>	5	\$10.50	10	50.8 [2.00]
<b>DN-11PLUG</b>	50	\$96.00	<b>DN-11PLUGMN</b>	5	\$11.50	11	55.9 [2.20]
<b>DN-12PLUG</b>	50	\$105.00	<b>DN-12PLUGMN</b>	5	\$12.00	12	61.0 [2.40]

Terminal Plugs Ratings	
<b>Voltage/Current</b>	300V, 12A
<b>Wire Gauge</b>	14–22 AWG, CU only
<b>Torque</b>	Tightening Torque: 0.51 N·m [4.5 lb·in]
<b>Usage Temperature</b>	Ambient air temperature: -20°C to 105°C [-4°F to 221°F] Relative humidity: 50% max at 40°C [104°F]; 90% max at 20°C [68°F]
<b>Agency Approvals</b>	UL file #: E179129


*Note: To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.*

\* DN-xxPLUGs fit all DN-EMXxx & DN-QEMXxx plug-in terminal blocks

## Disconnect Blade



**DN-DIS-BLADE  
DN-DIS-BMN**




Disconnect Blade			
Part Number	Description	Pcs/Pkg	Price
<b>DN-DIS-BLADE</b>	Terminal block disconnect blade for DN-FE2, DN-FE4, DN-DIS2 and DN-DIS4	50	\$22.00
<b>DN-DIS-BMN</b>		10	\$5.75

## End Brackets



End Brackets			
Part Number	Description	Pcs/Pkg	Price/Pkg
<b>DN-EB15</b>	Terminal block end stop 7mm width screw clamping. Gray	100	\$65.00
<b>DN-EB15MN</b>		20	\$14.50
<b>DN-EB35</b>	Terminal block end stop 9mm width screw clamping. Gray	50	\$40.00
<b>DN-EB35MN</b>		20	\$18.50
<b>DN-EB35-A</b>	Terminal block end stop 6mm width screw clamping. Black	50	\$28.50
<b>DN-EB35-A-10</b>		10	\$7.75
<b>DN-QEB35</b>	Terminal block end stop 6mm width screwless clamping. Black	50	\$25.50
<b>DN-QEB35-10</b>		10	\$7.75



For more information on accessories, see the "DINnectors Accessories" section of this chapter.



# DINnectors<sup>®</sup> Accessories

## End Covers

Certain end covers can be used with multiple terminal block parts to cover and insulate the open side, or to put more space between adjacent blocks.

DINnectors End Covers				
Part Number	Description	For Use With	Pcs/Pkg	Price
<b>DN-EC1210</b>	Covers open side of DN-T12-A and DN-T10-A series terminal blocks	DN-T10-A, DN-T12-A	100	\$26.00
<b>DN-EC1210MN</b>			25	\$8.25
<b>DN-EC86</b>	Covers open side of DN-T8 and DN-T6 series terminal blocks	DN-T8, DN-T6	100	\$28.00
<b>DN-EC86MN</b>			25	\$8.25
<b>DN-EC4</b>	Covers open side of DN-T4 series terminal blocks	DN-T4	50	\$17.50
<b>DN-EC4MN</b>			10	\$3.50
<b>DN-EC1/0</b>	Covers open side of DN-T1/0 series terminal blocks	DN-T1/0	50	\$20.00
<b>DN-EC1/0MN</b>			10	\$4.00
<b>DN-DEC10</b>	Covers open side of DN-D10 series double-level terminal blocks	DN-D10	100	\$18.50
<b>DN-DEC10MN</b>			10	\$3.75
<b>DN-EC14</b>	Covers open side of DN-TL14-A series terminal blocks	DN-TL14-A	25	\$10.50
<b>DN-EC14S</b>	Covers open side of DN-TL14S-A series terminal blocks	DN-TL14S-A	25	\$9.25
<b>DN-ECM10</b>	Covers open side of DN-M10-A series terminal blocks	DN-M10-A DN-M10B-A	100	\$26.00
<b>DN-ECM10MN</b>			25	\$8.25
<b>DN-ECKBD</b>	Covers open side of DN-KBD12 (MN) series disconnect blocks	DN-KBD12 (MN)	100	\$26.00
<b>DN-ECKBDMN</b>			10	\$3.75
<b>DN-EMXM1EC1</b>	Covers open side of DN-EMXM1 and DN-QEMXM1 terminal blocks	DN-EMXM1	25	\$8.75
<b>DN-EMXM1EC2</b>	Covers closed side of DN-EMXM1 and DN-QEMXM1 terminal blocks	DN-QEMXM1	25	\$8.75
<b>DN-EMXDVEC1</b>	Covers open side of DN-EMXDV and DN-QEMXDV terminal blocks	DN-EMXDV	25	\$8.75
<b>DN-EMXDVEC2</b>	Covers closed side of DN-EMXDV and DN-QEMXDV terminal blocks	DN-QEMXDV	25	\$8.75
<b>DN-FESEP</b>	Covers closed side of DN-FE sockets and DN-DIS disconnects	DN-FE, DN-DIS	50	\$15.50
<b>DN-FESEP-10</b>			10	\$3.00
<b>DN-QEC12</b>	Covers open side of DN-Q12-A or DN-QG12 series screwless terminal blocks	DN-Q12-A DN-QG12	50	\$12.50
<b>DN-QEC12MN</b>			10	\$3.25
<b>DN-QEC10</b>	Covers open side of DN-Q10-A or DN-QG10 series screwless terminal blocks	DN-Q10-A DN-QG10	50	\$12.50
<b>DN-QEC10MN</b>			10	\$3.25
<b>DN-QEC8</b>	Covers open side of DN-Q8-A or DN-QG8 series screwless terminal blocks	DN-Q8-A DN-QG8	50	\$14.50
<b>DN-QEC8MN</b>			10	\$3.50
<b>DN-QEC12-1-2</b>	Covers open side of DN-Q12-1-2-A and DN-QKBD12-A series screwless terminal blocks	DN-Q12-1-2-A, DN-QKBD12	25	\$9.00
<b>DN-QEC12-2-2</b>	Covers open side of DN-Q12-2-2-A series screwless terminal blocks	DN-Q12-2-2-A	25	\$10.00
<b>DN-QDEC12</b>	Covers open side of DN-QD12-A series screwless terminal blocks	DN-QD12-A	25	\$10.00

## Spacers

Spacers are used to put more space between adjacent blocks.

DINnectors Spacers				
Part Number	Description	For Use with	Pcs/Pkg	Price
<b>DN-S1210</b>	Spacer for DN-T12-A and DN-T10-A series terminal blocks	DN-T10-A DN-T12-A	100	\$31.00
<b>DN-S1210MN</b>			25	\$9.50
<b>DN-S86</b>	Spacer for DN-T8 and DN-T6 series terminal blocks	DN-T8 DN-T6	100	\$36.50
<b>DN-S86MN</b>			25	\$8.00
<b>DN-EMXM1SPA1</b>	Spacer for single-level plug-in terminal blocks	DN-EMXM1 DN-QEMXM1	25	\$7.50
<b>DN-EMXDVSPA1</b>	Spacer for double-level plug-in terminal blocks	DN-EMXDV DN-QEMXDV	25	\$8.50
<b>DN-FESPA</b>	Spacer for DN-FE sockets and DN-DIS disconnects	DN-FE DN-DIS	50	\$15.50
<b>DN-FESPA-10</b>			10	\$3.00

## Top Covers








DINnectors Top Covers				
Part Number	Description	For Use with	Pcs/Pkg	Price
<b>DN-C12</b>	Top cover, clear, printed electrical symbol.	DN-T12-A	100	\$37.00
<b>DN-C12MN</b>			25	\$8.00
<b>DN-C10</b>	Top cover, clear, printed electrical symbol.	DN-T10-A	100	\$37.00
<b>DN-C10MN</b>			25	\$8.00
<b>DN-C86</b>	Top cover, clear, printed electrical symbol.	DN-T8 DN-T6	100	\$37.00
<b>DN-C86MN</b>			25	\$8.00
<b>DN-DC10</b>	Top cover, clear, printed electrical symbol.	DN-D10	100	\$35.00
<b>DN-DC10MN</b>			25	\$8.00
<b>DN-MC10</b>	Top cover, clear, printed electrical symbol.	DN-M10	100	\$38.00
<b>DN-MC10MN</b>			25	\$8.00

# DINnectors® Accessories

## DINnector End Covers and Spacers Dimensions

Part Number		Length	Height	Thickness
<b>DN-EC1210</b>	<b>DN-EC1210MN</b>	44mm [1.73 in]	35mm [1.38 in]	1.5 mm [0.06 in]
<b>DN-S1210</b>	<b>DN-S1210MN</b>	55mm [2.17 in]	44mm [1.73 in]	
<b>DN-EC86</b>	<b>DN-EC86MN</b>	50mm [1.97 in]	43mm [1.69 in]	
<b>DN-S86</b>	<b>DN-S86MN</b>	55mm [2.17 in]	49mm [1.93 in]	
<b>DN-EC4</b>	<b>DN-EC4MN</b>	56mm [2.21 in]	48mm [1.89 in]	
<b>DN-EC1/O</b>	<b>DN-EC1/OMN</b>	62mm [2.44 in]	60mm [2.36 in]	
<b>DN-DEC10</b>	<b>DN-DEC10MN</b>	72mm [2.80 in]	49mm [1.93 in]	
<b>DN-EC14</b>	–	78mm [3.08 in]	55mm [2.17 in]	
<b>DN-EC14S</b>	–	55mm [2.17 in]	50mm [1.97 in]	
<b>DN-ECM10</b>	<b>DN-ECM10MN</b>	32mm [1.26 in]	27mm [1.06 in]	
<b>DN-ECKBD</b>	<b>DN-ECKBDMN</b>	52mm [2.05 in]	34.5 mm [1.36 in]	
<b>DN-EMXM1EC1</b>	<b>DN-EMXM1EC2</b>	as shown on next page		
<b>DN-EMXDVEC1</b>	<b>DN-EMXDVEC2</b>			
<b>DN-EMXDVSPA1</b>	<b>DN-EMXM1SPA1</b>			
<b>DN-FESPA</b>	<b>DN-FESPA-10</b>			
<b>DN-FESEP</b>	<b>DN-FESEP-10</b>			
<b>DN-QEC12</b>	<b>DN-QEC12MN</b>	50mm [1.97 in]	23mm [0.9 in]	1.5 mm [0.06 in]
<b>DN-QEC10</b>	<b>DN-QEC10MN</b>	57.4 mm [2.26 in]	33.6 mm [1.32 in]	
<b>DN-QEC8</b>	<b>DN-QEC8MN</b>	63mm [2.48 in]	38.5 mm [1.52 in]	
<b>DN-QEC12-1-2</b>	–	68.5 mm [2.70 in]	28.5 mm [1.12 in]	
<b>DN-QEC12-2-2</b>	–	87.5 mm [3.44 in]	28.5 mm [1.12 in]	
<b>DN-QDEC12</b>	–	98mm [3.86 in]	37mm [1.46 in]	


**DN-EC1210, DN-EC1210MN DN-EC86, DN-EC86MN DN-EC4 (MN), DN-EC1/O (MN), DN-ECKBD (MN), DN-S1210, DN-S1210MN, DN-S86 (MN)**




# **DINnectors** Accessories

## Dimensional Drawings


**DN-EMXM1EC1**




**DN-EMXM1EC2**




**DN-EMXDVSPA1**




**DN-EMXM1SPA1**




**DN-EMXDVEC1**



**DN-EMXDVEC2**



**DN-FESEP,  
DN-FESEP-10**



**DN-FESPA, DN-FESPA-10**

