DINnectors^{*} Thermocouple Terminal Blocks

- 35mm DIN-rail mountable
- UL E179129
- CE (EN 60947-1/ EN 60947-7-1)



DN-THERM1 (open) Series: EURO TC - 50 Volt



DN-THERM2 (open) Series: EURO TC - 300 Volt

DN-L or DN-LT

series

500/100

various



DN-THERM× (shown closed)

		01		(1°				
	Ordering Information							
Color		Part Number	Qty	Price	Part Number	Qty Price		
0		DN-THERM1	50	\$224.00	DN-THERM2	50	\$224.00	
Gray		DN-THERM1MN	10	\$54.00	DN-THERM2MN	10	\$50.00	
Technical Specifications								
Stripping	Length	20mm	n [0.79 in]		20r	nm [0.79 in]		
Tightenin	g Torque	0.099 N·n	n [0.875 lb·in]		0.099 N	I·m [0.875 lb·	in]	
UL Appro	val*	50V AC/DC	- 3	0-20 AWG	300V	10A	20-16 AWG	
Operating	Temperature	Relative			e: -20 to 105°C [-4 to 2 0°C [104°F]; 90% max		'F]	
SCCR Rai	ting	10kA per Table SB4.1, 2009, UL 508A, Maximum short circuit current rating for unmarked components						
CE Conformity CE (EN 60947-1 / EN 60947-7-1)								
Agency File # UL E179129								
			Access	ories				
End Cove	r			In	cluded			
	7.5 mm	<u>DN-R35S1</u>	10	\$39.00	<u>DN-R35S1</u>	10	\$39.00	
35mm	high	DN-R35S1-2	2	\$11.00	DN-R35S1-2	2	\$11.00	
DIN Rail	15mm	<u>DN-R35HS1</u>	10	\$68.00	<u>DN-R35HS1</u>	10	\$68.00	
	high	DN-R35HS1-2	2	\$16.50	DN-R35HS1-2	2	\$16.50	
		<u>DN-EB35</u>	50	\$74.00	<u>DN-EB35</u>	50	\$74.00	
		DN-EB35MN	20	\$34.50	DN-EB35MN	20	\$34.50	
End Braci	kote	<u>DN-EB35-A</u>	50	\$52.50	<u>DN-EB35-A</u>	50	\$52.50	
LIIU DI ACI	neis	DN-EB35-A-10	10	\$13.00	DN-EB35-A-10	10	\$13.00	
		DN-QEB35	50	\$47.00	DN-QEB35	50	\$47.00	
		DN-QEB35-10	10	\$12.50	DN-QEB35-10	10	\$12.50	
Angled St	upport Bracket	DN-ASB1	50	\$107.00	DN-ASB1	50	\$107.00	
		i e	1	1	1	1	1	

^{*}Copper wire only

Marking Tags

DN-THERM1 has no assigned amp rating; intended for use with thermocouple wires only. For more information on accessories, see the DINnectors Accessories section of this chapter.

DN-L or DN-LT

series

DN-THERMx operation **Clamping Yoke**


500/100

various


Overlap of thermocouple wires allows for universal connections.

Thermocouple terminal blocks are designed with only one screw clamp to provide suitable connections to thermocouple sensors. The **DN-THERM1** and **DN-THERM2** clamping yoke terminal blocks have been designed to accept any type of thermocouple lead connection within their rated wire size ranges. The thermocouple leads are simply stripped of their insulation to 20mm (0.79"), and then inserted into the terminal block where the two wires overlap. The leads are clamped together on both sides of the terminal block, resulting in an excellent electrical connection to the thermocouple without the need for any other compensation metals/ contacts.

DN-THERM1 / DN-THERM1MN



DN-THERM2 / DN-THERM2MN



tTBL-71

DINnectors Accessories

Marking Tags Cross Reference Charts - Screw-type

DINnec	DINnector Marking Tags Cross Reference - Screw-type					
Block Type	DN-L	DN-LA	DN-LT	DN-LAT	DN-EMLBL	
DN-T12	-	Х	Х	-	-	
DN-T10	Х	-	Х	-	-	
DN-T8	Х	_	Х	-	-	
DN-T6	Х	_	Х	-	-	
DN-T4	Х	_	Х	-	-	
DN-T1/0	Х	-	Х	-	-	
DN-T3/0	Х	-	Х	-	-	
DN-D10	Х	-	Х	-	-	
DN-D10X	Х	_	Х	-	_	
DN-D10LED	X	-	Х	-	-	
DN-D10DR	X	_	X	-	-	
DN-TL14	_	-	_	Χ	-	
DN-THERM	X	-	X	-	-	
DN-EMXM1	-	Х	X	-	Х	
DN-EMXDV	-	Х	X	-	Х	
DN-M10	-	-	X	-	-	
<u>DN-MG10</u>	-	-	X	-	-	
DN-G10	X	-	X	-	-	
DN-G8	X	-	X	-	-	
DN-G6	X	-	X	-	-	
DN-G4	X	-	X	-	-	
DN-G1/0	X	-	Х	-	-	
DN-F6	X	-	X	-	-	
DN-F10	X	_	Х	-	-	
DN-DIS2	_	X	X	-	-	
DN-DIS4	X	-	X	-	-	
DN-FE2	_	X	X	-	-	
DN-FE4	X	_	X	-	-	
DN-DIS10	X	_	X	-	-	
DN-KBD12	_	Х	X	-	-	

Continued on next page

www.automationdirect.com Terminal Blocks

DINnectors Accessories

Marking Tags


Marking Tags DN-L Series				
Part Number	Marking Sequence	Qty	Price	
DN-L50	1-50	500	\$61.50	
DN-L100	51-100	500	\$61.50	
DN-L150	101-150	500	\$61.50	
DN-L200	151-200	500	\$61.50	
DN-L250	201-250	500	\$61.50	
DN-L300	251-300	500	\$61.50	
DN-L350	301-350	500	\$61.50	
DN-L400	351-400	500	\$61.50	
DN-L450	401-450	500	\$61.50	
DN-LB	Blank	500	\$42.00	
DN-LS	L1, L2, L3, L, N, GND, +, -, COM,COM*	500	\$61.50	

Marking Tags DN-LA Series					
Part Number	Marking Sequence	Qty	Price		
DN-LA100	1-100	500	\$61.50		
DN-LA200	101-200	500	\$61.50		
DN-LA300	201-300	500	\$61.50		
DN-LA400	301-400	500	\$61.50		
DN-LAB	Blank Tags	500	\$61.50		
DN-LAS	L1, L2, L3, L, N, GND, +, -, COM,COM*	500	\$61.50		

Marking Tags DN-LAT Series					
Part Number	Marking Sequence	Qty	Price		
DN-LAT100-A	1-100	500	\$54.00		
DN-LAT200-A	101-200	500	\$54.00		
DN-LAT300-A	201-300	500	\$54.00		
DN-LAT400-A	301-400	500	\$54.00		
DN-LAT500-A	401-500	500	\$54.00		
DN-LAT600-A	501-600	500	\$54.00		
DN-LATB-A	Blank Tags	500	\$39.00		
DN-LATS-A	L1, L2, L3, L, N, +,-, COM,COM*	500	\$54.00		


Marking Tags DN-QL Series					
Part Number	Marking Sequence	Qty	Price		
DN-QL100	1-100	500	\$47.00		
DN-QL200	101-200	500	\$47.00		
DN-QL300	201-300	500	\$47.00		
DN-QL400	301.400	500	\$47.00		
DN-QL500	401-500	500	\$47.00		
DN-QLB	Blank Tags	500	\$39.50		
DN-QLS	L1, L2, L3, L, N, +,-, COM,COM*	500	\$54.00		

Dimensions



- The marking sequence of 50 tags (i.e. 101-150) is printed 10 times in each package of 500
- The DN-L tags fit all DINnectors 6mm wide and wider.
- There will be a gap between tags on blocks wider than 6mm.
- Material: Thermoplastic with heat embossed black print.

Dimensions




- The marking sequence of 100 tags (i.e. 1-100) is printed five times in each package of 500.
- The DN-LA tags fit all DINnectors 5mm wide and wider. There will be a gap between tags on blocks wider than 5mm.
- Material: Thermoplastic with heat embossed black print.

Dimensions



- The marking sequence of 500 tags (i.e. 1-100) is printed five times in each package of 500.
- Material: Thermoplastic with heat embossed black print.

Dimensions



- The marking sequence of 500 (i.e. 1-100) is printed five times in each package of 500.
- Material: Thermoplastic with heat embossed black print.

DINnectors Accessories

Marking Tags continued


	Marking Tags DN-LT Series				
Part Number	Marking Sequence	Qty	Price		
DN-LT15	1-5	100	\$11.00		
DN-LT60	6-0	100	\$11.00		
DN-LT1	1	100	\$11.00		
DN-LT2	2	100	\$11.00		
DN-LT3	3	100	\$11.00		
DN-LT4	4	100	\$11.00		
DN-LT5	5	100	\$11.00		
DN-LT6	6	100	\$11.00		
DN-LT7	7	100	\$11.00		
DN-LT8	8	100	\$11.00		
DN-LT9	9	100	\$11.00 \$11.00		
<u>DN-LT0</u> DN-LTBLNK	0 Unprinted	100	\$11.00 \$11.00		
DN-LTBLNK DN-LTA	A	100	\$11.00		
DN-LTA DN-LTB	В	100	\$11.00		
DN-LTC	C	100	\$11.00		
DN-LTD	D	100	\$11.00		
DN-LTE	E	100	\$11.00		
DN-LTF	F	100	\$11.00		
DN-LTG	G	100	\$11.00		
DN-LTH	Н	100	\$11.00		
DN-LTI	I	100	\$11.00		
DN-LTJ	J	100	\$11.00		
<u>DN-LTK</u>	К	100	\$11.00		
<u>DN-LTL</u>	L	100	\$11.00		
DN-LTM	M	100	\$11.00		
<u>DN-LTN</u>	N	100	\$11.00		
_	-	-	-		
<u>DN-LTP</u>	Р	100	\$11.00		
DN-LTQ	Q	100	\$11.00		
DN-LTR	R	100	\$11.00		
DN-LTS	S T	100	\$11.00 \$11.00		
DN-LTT	U	100	,		
<u>DN-LTU</u> <u>DN-LTV</u>	V	100	\$11.00 \$11.00		
DN-LTV DN-LTW	W	100	\$11.00		
DN-LTX	X	100	\$11.00		
DN-LTY	Y	100	\$11.00		
DN-LTZ	Z	100	\$11.00		
DN-LTGND	<u> </u>	100	\$11.00		
DN-LTPOS	+	100	\$11.00		
DN-LTNEG	-	100	\$11.00		
DN-LTAC	~	100	\$11.00		
DN-LTDC	=	100	\$11.00		



- These marking tags allow the flexibility of creating custom marking sequences on site.
- The DN-M series supports a maximum of three digits (tags), while other DINnectors support up to four digits (tags).
- Material: Thermoplastic with heat embossed black print.

DN-MTA marking tag adapter

DN-MTA dimensions



Part Number	Description	Qty	Price
DN-MTA	Marking tag adapter holds up to six DN-LT tags	50	\$16.00

Note: <u>DN-MTA</u> adapter does not fit <u>DN-T12-A</u> terminal blocks.

DINnectors Accessories

Terminal Marking Accessories







DN-EMLBL3

Part Number	Description	For Use With	Qty	Price
DN-EMLBL1	Blank labels	DN-EMPEG1 pin protectors for DN-xEMXxx plug-in terminal	100	\$10.00
DN-EMLBL2	Labels printed 1 – 12		100	\$14.50
DN-EMLBL3	Labels printed 13 – 24	blocks	100	\$14.50

Description


Marking Pen – for terminal and wire marking tags

Part

Number

DN-MP

- Permanent
- Smudge-proof
- Waterproof
- Weatherproof
- Lightfast (won't fade)
- Dries in seconds (excellent for left-handed users)
- Dry-safe (pen can be left uncapped for days without drying out)
- · Low odor ink



Marking pen

Wire Marking Accessories



DN-WM-x wire tag holders

Part Number	Description	For Use With	Qty	Price
DN-WMTAG1	Wire tag – blank	all DN-WM-x wire tag holders	525	\$66.00
<u>DN-WM-1</u>	Wire tag holder, clear, 12mm length, 0.051–0.118 in diameter; for 22–16 AWG wire	DN-WMTAG1	200	\$14.00
DN-WM-2	Wire tag holder, clear, 12mm length, 0.098–0.196 in diameter; for 16-11 AWG wire		200	\$14.00
DN-WM-3	Wire tag holder, clear, 12mm length, 0.157–0.393 in diameter; for 13–5 AWG wire		100	\$9.00
DN-WM-4	Wire tag holder, clear, 12mm length, 0.314–0.629 in diameter; for 5AWG wire		100	\$8.50

www.automationdirect.com **Terminal Blocks** tTBL-75