

DYMO

Industrial Labeling Solutions

DYMO XTL Label Makers and Labels

XTL series label makers simplify industrial labeling with a large, viewable screen, intuitive controls, and a wide range of functions. XTL series label makers can print using continuous tape, presized labels, heat-shrink tubes, and small format safety labels.

The XTL 300 is a smaller, lighter system ideal for on-the-go label making, capable of printing up to 1 inch [24mm] wide labels.

The XTL 500 boasts a touch screen, more features, and the ability to print up to 2-1/8 inch [54mm] wide labels.

XTL labels come as all-in-one cartridges with the labels and printing tape rolled up inside. As long as your label maker is charged and a cartridge contains labels, you'll always be able to print.



Features

- Life-like on-screen print preview
- Built-in label applications
- Pre-loaded label templates
- 3-year limited warranty on label makers
- 1-year limited warranty on label cartridges
- Free DYMO ID configuration software
- Connect to PC to transfer labels to and from DYMO ID software
- Impact-resistant rubber bumpers and wipe-clean keypad
- Detects and displays label information when cartridge is inserted
- Supports barcode types Code 128 [Auto], Code 39 Mod 43, EAN8, EAN13, UPC-A, Codabar, PDF-417, and QR Code
- Labels work for countless applications, including any flat surface on terminal blocks and terminal block systems
- Customizable printer settings
- Adjustable text size
- Prints via thermal transfer
- 300 DPI print resolution
- Works with Windows 7 and later

DYMO Label Maker Applications		
Application	XTL 300	XTL 500
Arc Flash	–	√
Asset Tracking	√	√
Breaker	√	√
Cable Wrap	√	√
Distribution Panel	√	√
Flag	√	√
General Label	√	√
Heat-Shrink Tube	√	√
Materials Management	√	√
Patch Panel	√	√
Pipe Marking	–	√
Quick Label	√	√
Safety	–	√

DYMO

Industrial Labeling Solutions

DYMO XTL 300 Hand-held Label Maker

The XTL 300 label maker provides a compact, feature-rich labeling solution for labels up to 1 inch [24mm] wide. The XTL 300 is ideal for general identification, barcodes [1D and 2D], asset tracking, wire and cable identification, networking components identification, and facilities identification.

Features

All the standard features of XTL series label makers plus:

- Press-button cutting blade
- 2.8 inch color display
- 1.25 inch/second print speed
- Up to 11 printable lines
- Up to 1 inch [24mm] wide labels
- Replaceable cutter mechanism
- Replaceable battery
- 3-year limited warranty

See the labels section for all the label options compatible with the XTL 300 label maker.

The XTL 300 can be purchased with or without a carrying case.

System Contents

The XTL 300 label maker comes standard with:

- XTL 300 Label Maker
- AC Charging Adapter
- 48 inch USB Cable
- Rechargeable Lithium Polymer Battery
- (1) 1in x 23ft All-Purpose vinyl, black/white label tape
- Lanyard
- Quick Start Guide
- Software Download Card

XTL 300 [1868814]



The kit adds the following:

- Carrying case
- (1)] 13/16 inch x 1-9/16 inch Laminated Wire/Cable Wraps, black/white, 150 labels

DYMO XTL 300 Series Label Maker

Part Number	Price	Description
1868814	Retired	Dymo XTL 300 Series Hand-held Label Maker Kit. Includes charger, USB cable, rechargeable battery, 1in x 23ft all-purpose vinyl label tape, 13/16 in x 1-9/16 in laminated wire/cable wrap labels (150), and carrying case.
1888632	Retired	Replacement AC Power adapter for XTL 300 series
1814308	Retired	Replacement battery for XTL 300 series

DYMO

Industrial Labeling Solutions

DYMO XTL 500 Hand-held Label Maker

The XTL 500 label maker provides an enhanced, robust label making solution for labels up to 54mm [2-1/8"] wide. The XTL 500 is ideal for general identification, barcodes [1D and 2D], asset tracking, data communications identification, and MRO/facilities identification and communication.

XTL 500 [1868815]

Features

All the standard features of XTL series label makers plus:

- Automatic label cutting
- 4" color touch screen
- 1.10"/second print speed
- Up to 24 printable lines
- Up to 54mm [2-1/8"] wide labels
- Replaceable cutter mechanism
- Replaceable battery
- Compatible with DYMO safety labels
- Compatible with DYMO heat-shrink pre-sized labels
- 3-year limited warranty

See the labels section for all the label options compatible with the XTL 500 label maker.

System Contents

The XTL 500 label maker comes standard with:

- XTL 500 Label Maker
- AC Charging Adapter
- 48 inch USB Cable
- Rechargeable Lithium Polymer Battery
- (1) 2" x 23 ft All-Purpose vinyl, black/white label tape
- (1) 1-1/2" x 1-9/16" Laminated Wire/Cable Wraps, black/white, 150 labels
- Quick Start Guide
- Software Download Card
- Carrying case



DYMO XTL 500 Series Label Maker

Part Number	Price	Description
1868815	Retired	Dymo XTL 500 Series Hand-held Label Maker Kit. Includes charger, USB cable, rechargeable battery, 2in x 23ft all-purpose vinyl label tape, 1-1/2 in x 1-9/16 in laminated wire/cable wrap labels (150), and carrying case.
1888635	Retired	Replacement AC Power adapter for XTL 500 series
1888637	Retired	Replacement cutter mechanism for XTL 500 series
1888636	Retired	Replacement battery for XTL 500 series

DYMO

Industrial Labeling Solutions

DYMO Labels

XTL Heat-Shrink Tube

DYMO heat-shrink tube labels provide insulation when shrunk down and ensure a secure fit on wires and cables with a 3:1 shrink ratio. Constructed of flame-retardant polyolefin. Available in sizes from 1/4 inch to 1 inch wide, with black text on a white background.



Heat-shrink Tube
Continuous Label
Tape



Heat-shrink Tube
Pre-sized
Labels

DYMO Heat-Shrink Tube Label Tape

Part Number	Price	Description	Nominal Width inches	Actual Width inches [mm]	Material	Text Color	Background Color	Quantity	Compatibility
1868809	Retired	Heat-shrink tube label tape	1/4	0.24 [6]	Polyolefin	Black	White	[1] 8.9 ft roll	XTL 300 or 500
1868810	Retired		1/2	0.48 [12]					
1868811	Retired		1	0.94 [24]					

Note: See the "DYMO Label Usage Guide" for cable diameters suitable for each label type.

DYMO Heat-Shrink Tube Pre-sized Labels

Part Number	Price	Description	Nominal Width inches	Actual Width inches [mm]	Length inches	Material	Text Color	Background Color	Quantity	Compatibility
1868717	Retired	Heat-shrink tube pre-sized labels	1/4	0.24 [6]	1-5/16	Polyolefin	Black	White	81 labels	XTL 500
1868731	Retired				1-7/8				81 labels	
1868719	Retired		1	0.94 [24]	1-5/16				60 labels	

Note: See the "DYMO Label Usage Guide" for cable diameters suitable for each label type.

DYMO

Industrial Labeling Solutions

DYMO Labels

XTL All-Purpose Labels

DYMO all-purpose vinyl labels are ideal for almost any labeling application. Vinyl provides moisture, chemical, and UV resistance for both indoor and outdoor applications. Available in sizes from 1/2 in to 2in wide and a variety of text and background colors.



All-Purpose Continuous Label Tape

DYMO All-Purpose Label Tape Cartridge									
Part Number	Price	Description	Nominal Width inches	Actual Width inches [mm]	Material	Text Color	Background Color	Quantity	Compatibility
1868741	Retired	All-purpose label tape cartridge	1/2	0.48 [12]	Vinyl	Black	Clear	[1] 23 ft roll	XTL 300 or 500
1868751	Retired					Black	White		
1868761	Retired					White	Red		
1868771	Retired					Black	Yellow		
1868796	Retired					White	Black		
1868752	Retired					Black	White		
1868772	Retired		Black	Yellow		[1] 23 ft roll	XTL 300 or 500		
1868743	Retired		1	0.94 [24]		Black	Clear	[1] 23 ft roll	XTL 300 or 500
1868753	Retired					Black	White		
1868763	Retired					White	Red		
1868773	Retired					Black	Yellow		
1868778	Retired					White	Blue		
1868798	Retired					White	Black		
1868774	Retired		Black	Yellow		[1] 23 ft roll	XTL 500		
1868745	Retired		1-1/2	1.5 [38]		Black	Clear	[1] 23 ft roll	I XTL 500
1868755	Retired					Black	White		
1868765	Retired					White	Red		
1868775	Retired					Black	Yellow		
1868780	Retired					White	Blue		
						Black	Clear		
		Black	White						
		White	Red						
		Black	Yellow						
		White	Blue						

DYMO

Industrial Labeling Solutions

DYMO Labels

XTL Permanent Flat Surface Labels

DYMO permanent flat surface labels have a glossy finish and are ideal for labeling flat surfaces like panels, blocks, faceplates, and shelves. Constructed of polyester. Available in sizes from 1/4 in to 1/2in wide with black text on white or clear backgrounds.



DYMO Permanent Flat Surface Label Tape

Part Number	Price	Description	Nominal Width inches	Actual Width inches [mm]	Material	Text Color	Background Color	Quantity	Compatibility
1868735	Retired	Permanent flat surface label tape	1/4	0.24 [6]	Polyester	Black	White	[1] 29.8 ft roll	XTL 300 or 500
1868736	Retired		3/8	0.35 [9]		Black	White		
1868739	Retired		1/2	0.48 [12]		Black	Clear		
1868737	Retired		1/2	0.48 [12]		Black	White		



Industrial Labeling Solutions

DYMO Labels

XTL Laminated Wire/Cable Wrap

DYMO pre-sized wire/cable wraps have a laminated overwrap that protects against oil, chemicals, moisture, abrasion, and fading. In addition to the XTL-compatible label cartridges, laminated wire/cable wrap labels are available in sheets compatible with standard laser printers. Constructed of vinyl [XTL cartridges] or polyester [printer label sheets]. Available in sizes from 13/16 in to 1-1/2 in wide, with black text on a white background.



Laminated Wire/
Cable Wrap



Laser Printer Sheets

DYMO Laminated Wire/Cable Wrap Pre-sized Labels										
Part Number	Price	Description	Nominal Width inches	Actual Width inches [mm]	Length inches	Material	Text Color	Background Color	Quantity	Compatibility
<u>1868704</u>	Retired	Laminated wire/cable wrap pre-sized labels	13/16	0.83 [21]	13/16	Vinyl	Black	White	250 labels	XTL 300 or 500
<u>1868705</u>	Retired				1-9/16				150 labels	
<u>1868706</u>	Retired				4				75 labels	
<u>1908552</u>	Retired		1	0.94 [24]	7/8	Polyester	n/a	White	2592 labels	Laser Printer
<u>1868707</u>	Retired		1-1/2	1.5 [38]	13/16	Vinyl	Black	White	250 labels	XTL 500
<u>1908556</u>	Retired				1-5/8				Polyester	n/a

Note: See the "DYMO Label Usage Guide" for cable diameters suitable for each label type.

DYMO

Industrial Labeling Solutions

DYMO Labels

XTL Flexible Cable Wrap

DYMO flexible cable wrap is ideal for labeling cables, wires, and other rounded surfaces. Constructed of flexible, tear-proof nylon. Available in sizes from 1/2 inch to 1 inch wide, with black text on a white background.



Flexible Cable
Wrap

DYMO Flexible Cable Wrap Label Tape

Part Number	Price	Description	Nominal Width inches	Actual Width inches [mm]	Material	Text Color	Background Color	Quantity	Compatibility
<u>1868806</u>	Retired	Flexible cable wrap label tape	1/2	0.48 [12]	Flex Nylon	Black	White	[1] 18 ft roll	XTL 300 or 500
<u>1868807</u>	Retired		3/4	0.75 [19]					
<u>1868808</u>	Retired		1	0.94 [24]					



Industrial Labeling Solutions

DYMO Label Usage Guide

Use the table below to determine which type of DYMO label is suitable for a given application.

DYMO Label Usage Guide							
Surface	All-Purpose Vinyl	Permanent Flat Surface	Flexible Cable Wrap	Heat-Shrink Tube	Laminated Wire/Cable Wraps	Pre-Sized Labels	Pre-Sized Safety Labels
Flat	√	√	√	-	-	√	√
Wires & Cables	√	-	√	√	√	-	-
Curved	√	-	√	-	-	-	-
Flag	√	-	√	-	-	-	-
Textured	√	√	√	-	-	√	√
Resistance	All-Purpose Vinyl	Permanent Flat Surface	Flexible Cable Wrap	Heat-Shrink Tube	Laminated Wire/Cable Wraps	Pre-Sized Labels	Pre-Sized Safety Labels
Heat/Cold	-40 to 140 °F	-40 to 140 °F	-40 to 140 °F	Max. 257 °F	-40 to 140 °F	-40 to 140 °F	-40 to 140 °F
Outdoor	√	√	-	-	-	√	√
UV Light	√	√	√	√	√	√	√
Oil	√	√	-	√	√	√	-
Water	√	√	-	√	√	√	√
Chemical	√	√	-	√	√	√	-

DYMO Label Sizing Guide

Use the tables below to determine which size of DYMO label you need for a given application. Note that for heat-shrink tubing, if your cable diameter is less than the minimum value listed, the tubing will not shrink tightly enough to make a seal.

DYMO Heat-shrink Tube Sizing Guide							
DYMO Heat-shrink Tube Width		Minimum Cable Diameter		Maximum Cable Diameter		Minimum AWG	Maximum AWG
in	mm	in	mm	in	mm		
0.250	6	0.050	1.273	0.150	3.820	16	7
0.375	9	0.075	1.910	0.226	5.730	12	4
0.500	12	0.100	2.546	0.301	7.639	10	1
0.750	19	0.159	4.032	0.476	12.096	6	4/0+
1.000	24	0.201	5.093	0.602	15.279	4	4/0+
2.000	54	0.45	11.35	1.34	34.06	-	-

DYMO Pipe Marker Sizing Guide					
Outside Pipe Diameter		Minimum Label Length		Minimum Letter Height	
in	mm	in	mm	in	mm
0.75-1.25	19-32	8	200	0.50	13
1.50-2	38-51	8	200	0.75	19
2.50-6	64-150	12	300	1.25	32
8-10	200-250	24	600	2.50	64
> 10	> 250	32	800	3.50	89



Industrial Labeling Solutions

DYMO Label Visual Guide

The graphic below provides samples of what different DYMO labels look like set up for various uses.

DYMO LABELS: A VISUAL GUIDE

LABEL WIDTHS

NETWORKING COMPONENTS

A01 | A02 | A03 | A04

PRE-SIZED LABELS

1668655 / 1/2" x 1/2" 1668666 / 1/2" x 1"

PRE-SIZED HEAT-SHRINK TUBE

A-01-01

1668733 / 1" x 1 7/8" Black on White

PERMANENT FLAT SURFACE

A-01 | A-02 | A-03 | A-04 | A-05 | A-06

1668736 / 3/8" Black on White

SAFETY & WARNINGS

CAUTION

WARNING

DANGER

NOTICE

LAMINATED WIRE/CABLE WRAPS

A-01

1668708 / 1-1/2" x 1-9/16"

COLOR CODING

COLOR

CODE

YOUR

FILES

PRE-SIZED SAFETY LABELS

NOTICE

1668715 / 2" x 4"

1668714 / 2" x 4"

1/2" DRILL BITS

1668740 / 1/2" Black on Clear

ALL-PURPOSE VINYL COLORS

ASSET TRACKING

This book is property of
Park Grove Elementary
PLEASE RETURN

LC 3501.M3 A8 1966

BARCODING

3 007 1701184840

12345

1668667 1/2" x 1-1/2"

GENERAL IDENTIFICATION

Expense Reports | Jan - Mar | 2014

KEEP DOOR LOCKED

MEET STANDARDS

Recognized

Compliant RoHS

5S VISUAL WORKPLACE

PIPE MARKING

→ **POTABLE WATER** →



Industrial Labeling Solutions

DYMO Label Standards Guide

The graphic below provides examples of label configurations and how they meet ANSI and ISO standards.

↓ COLORS	STANDARDS →			
	ANSI Z535 Visual Workplace	ISO 3864 Visual Workplace	ISO 7010 Graphical Symbols	ANSI A13.1 Pipemarking
Black on White	General ID	Supplementary Information	—	—
White on Red	Danger	Danger, Prohibition, Fire Safety	Prohibition, Fire Safety	Fire Quenching
Black on Orange	Warning	Warning	—	Toxic and Corrosive Fluid
Black on Yellow	Caution	Caution, Triangular Warning Symbols	Warning	Flammable Fluids
White on Green	Instruction	Safe Conditions	Safe Conditions	Potable Water
White on Blue	Notice	Mandatory Action	Mandatory Action	Compressed Air
White on Purple	Safety	—	—	—
White on Brown	—	—	—	Combustible Fluids
White on Black	General ID	—	—	—
Black on Gray	General ID	—	—	—