

Floor Stand Kits and Stabilizers



Floor Stand Kits

Floor stand kits can be used to support most wall-mounted Wiegmann enclosures or to elevate freestanding enclosures.

Each kit includes two floor stands and mounting nuts and bolts. Floor stands are installed by drilling holes in the bottom of the enclosure and bolting the floor stands in place.



SSFK1216

Stainless steel floor stand is type 304, 10 gauge stainless with a grained finish.




FK0608

Steel floor stand has ANSI 61 gray polyester powder finish over phosphatized surfaces.

| Shipping Schedule | | | | |
|--|------------|------------|-------------|-------------|
| Same day | 1 - 5 days | 1 - 7 days | 1 - 15 days | 1 - 20 days |
| Color indicates shipping lead time in business days. | | | | |

| Steel Floor Stand Kit | Price | Wt.[lb] | Stainless Steel Floor Stand Kit | Price | Wt.[lb] | Floor Stand Height "H" | Enclosure Depth "D" |
|------------------------|----------|---------|---------------------------------|------------|---------|------------------------|---------------------|
| FK0608 | \$145.00 | 19 | SSFK0608 | \$550.00 | 19 | 6 [152] | 8 [203] |
| FK0610 | \$159.00 | 21 | SSFK0610 | \$603.00 | 21 | 6 [152] | 10 [254] |
| FK0612 | \$182.00 | 23 | SSFK0612 | \$573.00 | 23 | 6 [152] | 12 [305] |
| FK0618 | \$216.00 | 31 | SSFK0618 | \$657.00 | 31 | 6 [152] | 18 [457] |
| FK0624 | \$294.00 | 50 | SSFK0624 | \$898.00 | 33 | 6 [152] | 24 [610] |
| FK1208 | \$188.00 | 29 | SSFK1208 | \$623.00 | 30 | 12 [305] | 8 [203] |
| FK1210 | \$202.00 | 34 | SSFK1210 | \$670.00 | 27 | 12 [305] | 10 [254] |
| FK1212 | \$216.00 | 37 | SSFK1212 | \$632.00 | 38 | 12 [305] | 12 [305] |
| FK1216 | \$244.00 | 42 | SSFK1216 | \$811.00 | 35 | 12 [305] | 16 [406] |
| FK1218 | \$258.00 | 45 | SSFK1218 | \$891.00 | 38 | 12 [305] | 18 [457] |
| FK1220 | \$272.00 | 50 | SSFK1220 | \$1,034.00 | 40 | 12 [305] | 20 [508] |
| FK1224 | \$286.00 | 60 | SSFK1224 | \$1,058.00 | 43 | 12 [305] | 24 [610] |
| FK1808 | \$249.00 | 40 | — | — | — | 18 [457] | 8 [203] |
| FK1810 | \$244.00 | 45 | — | — | — | 18 [457] | 10 [254] |
| FK1812 | \$258.00 | 50 | — | — | — | 18 [457] | 12 [305] |
| FK1816 | \$287.00 | 58 | — | — | — | 18 [457] | 16 [406] |
| FK2408 | \$272.00 | 52 | — | — | — | 24 [610] | 8 [203] |
| FK2410 | \$287.00 | 56 | SSFK2410 | \$952.00 | 57 | 24 [610] | 10 [254] |
| FK2412 | \$301.00 | 60 | SSFK2412 | \$998.00 | 61 | 24 [610] | 12 [305] |

Notes: Dimensions in inches (millimeters).
Letters in table correspond to letters on dimensional drawings.



Stabilizers

Designed to prevent injury to workers by stabilizing floor mounted enclosures which are not bolted down. Stabilizers slip under the floor stands and are secured with bolts.

| Stabilizers | Price | Description | Wt.[lb] |
|------------------------|----------|---|---------|
| WAENST | \$171.00 | Wiegmann enclosure stabilizer, ANSI 61 gray powder coat finish. Use to prevent tipping of floor mounted enclosures which are not bolted down. Package of 2. | 29 |

Dimensions

