

Rack Mount Fan Trays



Fan Tray p/n [019310-00](#)

Applications

Compact high performance fan tray for forced circulation of air in switch and server enclosures and for concerted cooling of 19in. rack mounted component groups. Natural convection is improved and the formation of localized hot pockets is avoided.

Features

- High air output
- Long service life
- Ball bearing fans
- Ready for connection. Plug included, cable required.
- Optical function indicator
- 115VAC Operating Voltage
- UL Recognized File: E234324



General Specifications	
Axial fans, ball bearing	Service life 50,000 hr at 25°C (77°F), 65 % RH
Material	Front panel: aluminum, bright anodized; casing: steel sheet, electro-galvanized
Optical indicator	Integrated in front panel
Connection	Appliance power inlet on rear of casing, plug included
Fitting position	Vertical airflow (air outlet up)
Operating/Storage temperature	-10 to 60°C (14 to 140°F) / -40 to 70°C (-40 to 158°F)
Operating/Storage humidity	Max. 90 % RH (non-condensing)
Protection type	IP20

Rack Mount Fan Trays			
Part Number	Price	Airflow (CFM)	Drawing Links
019310-00	\$211.00	339	PDF
019510-00	\$653.00	1016	PDF