

# Fuji Molded Case Circuit Breakers – Products And Accessory Compatibility

Match the Accessories with Fuji Molded Case Circuit Breakers						
Part Number	Description	BW125JAGU	BW250JAGU	BW400SAGU	BW630RAGU	BW800RAGU
<b>BW9W1SGO</b>	Auxiliary Switch (Mounting Left and right side)	X	X			
<b>BW9W1SHA</b>	Auxiliary Switch (Mounting Left side ONLY)			X	X	X
<b>BW9FRGO</b>	Shunt Trip 24 VAC/VDC (Mounting both Left and Right sides)	X	X			
<b>BW9FHA-R</b>	Shunt Trip 24-48 VAC/VDC (Mounting Left side ONLY)			X	X	X
<b>BW9FAGO</b>	Shunt Trip 100-120 VAC, 100-110 VDC (Mounting both Left and Right sides)	X	X			
<b>BW9FHA-A</b>	Shunt Trip 100-280 VAC, 100-220 VDC (Mounting Left side ONLY)			X	X	X
<b>BW9RGAR</b>	UnderVoltage Release 24VDC (Left side ONLY)	X	X			
<b>BW9RHA-R</b>	UnderVoltage Release 24 VAC/VDC (Left side ONLY)			X	X	X
<b>BW9RGAT</b>	UnderVoltage Release 110-130 VAC (Left side ONLY)	X	X			
<b>BW9RHA-1</b>	UnderVoltage Release 120-130 VAC, 125VDC (Left side ONLY)			X	X	X
<b>BW9SLOCA-3</b>	Replacement Lugs Kit for 125 Amp frame	X				
<b>BW9SLOGA-3</b>	Replacement Lugs Kit for 250 Amp frame up to 175A		X			
<b>BW9SL1GA-3</b>	Replacement Lugs Kit for 250 Amp frame 200A to 250A		X			
<b>BW9V0CA</b>	Rotary Handle	X				
<b>BW9V0GA</b>	Rotary Handle		X			
<b>BW9VSGO</b>	Optional Shaft for BW9V0CA and BW9V0GA, 6.063"	X	X			
<b>BW9VSGO-24</b>	Optional Shaft for BW9V0CA and BW9V0GA, 24"	X	X			
<b>BW9V0HA</b>	Rotary Handle,			X		
<b>BW9V0JA</b>	Rotary Handle,				X	X
<b>BZ-VS2</b>	Optional Shaft for BW9V0HA and BW9V0JA, 3.48"			X	X	X
<b>BZ-VS2-24</b>	Optional Shaft for BW9V0HA and BW9V0JA, H = 24"			X	X	X
<b>BW9FOCA-15A</b>	Flange Handle (flex shaft), NEMA 12, 59" (1.5m) cable, 125 Amp frame	X				
<b>BW9FOCA-20A</b>	Flange Handle (flex shaft), NEMA 12, 78.7" (2.0m) cable, 125 Amp frame	X				
<b>BW9FOGA-15A</b>	Flange Handle (flex shaft), NEMA 12, 59" (1.5m) cable, 250 Amp frame		X			
<b>BW9FOGA-20A</b>	Flange Handle (flex shaft), NEMA 12, 78.7" (2.0m) cable, 250 Amp frame		X			
<b>BW9FOHA-15A</b>	Flange Handle (flex shaft), NEMA 12, 59" (1.5m) cable, 400 Amp frame			X		
<b>BW9FOHA-20A</b>	Flange Handle (flex shaft), NEMA 12, 78.7" (2.0m) cable, 400 Amp frame			X		
<b>BW9FOJA-15A</b>	Nema 12 flexible shaft handle for 630A or 800A frame. 59.06" (1.5m) cable				X	X
<b>BW9FOJA-20A</b>	Nema 12 flexible shaft handle for 630A or 800A frame. 78.74" (2m) cable				X	X
<b>BW9BTJA-L3W</b>	Terminal Cover for the 400A frame			X		
<b>BW9BTJA-L3W</b>	Terminal Cover for the 630A AND 800A frame				X	X
<b>BW9Q1CA</b>	Lockout Attachment 125A and 250A frames	X	X			
<b>BW9QNHA</b>	Lockout Attachment 400A, 630A and 800A frames			X	X	X

### Internal Accessory Combinations for BW Series



MCCB	BW125 BW250	BW400 BW630 BW800
Pole	3	3
Auxiliary switch	○ □	○ □
SPDT	□	□
Shunt trip	□	□
Undervoltage trip	■ □	■ □
Auxiliary Switch + Shunt Trip	○ □ □	○ □ □
Undervoltage + Auxiliary Switch	■ □ ○	■ □ ○