

FIBOX

Enclosing innovations

MNX Series Polycarbonate Miniature Cases with Knockouts

**ULPCM12560T****ULPCM12575G**

Features

- Includes gasketed cover with 2-component molded construction and TPE/PUR gasket system
- Premium thick-wall polycarbonate design with reinforced corner construction
- Cover contains corrosion-free polyamide screws
- Easy wall mounting using optional mounting foot kits and through-base mounting holes using included mounting screws
- Optional galvanized steel back panels and DIN-35 mounting rails available as accessories

Construction

- Molded from RAL 7035 light gray and/or smoked transparent, impact-resistant polycarbonate
- Gasket material is TPE (Thermoplastic Elastomer) or PUR (Polyurethane)
- Temperature range -40 to +250 °F [-40 to +120 °C]
- Metric knock-outs sized from M12 to M50 molded in place for immediate cable entry access

Listings

- UL/cUL UL508A Type 1, 4, 4X and 6 [File E75645]
- Complies with NEMA Type 1, 4, 4X and 6
- Ingress Protection (EN 60529) IP66/IP67
- Impact Resistance (EN 62262) IK08



MNX Series Polycarbonate Miniature Cases with Knockouts

Smoked Cover	Price	Opaque Cover	Price	Enclosure Size HxWxD	Cover Depth	Drawing Link	Front Swing Panel*	Price	Subpanel	Price
ULPCM9560T	\$37.00	ULPCM9560G	\$36.50	3.94 x 3.94 x 2.36 [100 x 100 x 60]	0.39 [10]	PDF	—	—	MIV95	\$3.25
ULPCM9575T	\$38.00	ULPCM9575G	\$37.00	3.94 x 3.94 x 3.03 [100 x 100 x 77]	1.06 [27]	PDF	—	—	MIV95	\$3.25
ULPCM10060T	\$38.50	ULPCM10060G	\$38.00	5.12 x 3.15 x 2.40 [130 x 80 x 61]	0.43 [11]	PDF	—	—	MIV100	\$3.00
ULPCM10075T	\$39.00	ULPCM10075G	\$38.00	5.12 x 3.15 x 3.03 [130 x 80 x 77]	1.06 [27]	PDF	—	—	MIV100	\$3.00
ULPCM100100T	\$40.00	ULPCM100100G	\$38.50	5.12 x 3.15 x 4.02 [130 x 80 x 102]	2.05 [52]	PDF	—	—	MIV100	\$3.00
ULPCM100125T	\$40.50	ULPCM100125G	\$40.50	5.12 x 3.15 x 5.00 [130 x 80 x 127]	3.03 [77]	PDF	—	—	MIV100	\$3.00
ULPCM12560T	\$45.50	ULPCM12560G	\$45.00	5.12 x 5.12 x 2.40 [130 x 130 x 61]	0.43 [11]	PDF	—	—	MIV125	\$3.75
ULPCM12575T	\$47.00	ULPCM12575G	\$46.50	5.12 x 5.12 x 3.03 [130 x 130 x 77]	1.06 [27]	PDF	—	—	MIV125	\$3.75
ULPCM125100T	\$47.50	ULPCM125100G	\$47.00	5.12 x 5.12 x 4.02 [130 x 130 x 102]	2.05 [52]	PDF	—	—	MIV125	\$3.75
ULPCM125125T	\$49.00	ULPCM125125G	\$48.50	5.12 x 5.12 x 5.00 [130 x 130 x 127]	3.03 [77]	PDF	—	—	MIV125	\$3.75
ULPCM15060T	\$54.00	ULPCM15060G	\$54.00	7.09 x 5.12 x 2.40 [180 x 130 x 61]	0.43 [11]	PDF	—	—	MIV150	\$4.50
ULPCM15075T	\$55.00	ULPCM15075G	\$55.00	7.09 x 5.12 x 3.03 [180 x 130 x 77]	1.06 [27]	PDF	—	—	MIV150	\$4.50
ULPCM150100T	\$56.00	ULPCM150100G	\$56.00	7.09 x 5.12 x 4.02 [180 x 130 x 102]	2.05 [52]	PDF	—	—	MIV150	\$4.50
ULPCM150125T	\$58.00	ULPCM150125G	\$58.00	7.09 x 5.12 x 5.00 [180 x 130 x 127]	3.03 [77]	PDF	—	—	MIV150	\$4.50
ULPCM150150T	\$63.00	ULPCM150150G	\$62.00	7.09 x 5.12 x 5.98 [180 x 130 x 152]	4.02 [102]	PDF	—	—	MIV150	\$4.50
ULPCM17560T	\$69.00	ULPCM17560G	\$69.00	7.09 x 7.09 x 2.40 [180 x 180 x 61]	0.43 [11]	PDF	FPA175180	\$19.00	MIV175	\$5.25
ULPCM17575T	\$71.00	ULPCM17575G	\$69.00	7.09 x 7.09 x 3.03 [180 x 180 x 77]	1.06 [27]	PDF	FPA175180	\$19.00	MIV175	\$5.25
ULPCM175100T	\$72.00	ULPCM175100G	\$71.00	7.09 x 7.09 x 4.02 [180 x 180 x 102]	2.05 [52]	PDF	FPA175180	\$19.00	MIV175	\$5.25
ULPCM175125T	\$79.00	ULPCM175125G	\$77.00	7.09 x 7.09 x 5.00 [180 x 180 x 127]	3.03 [77]	PDF	FPA175180	\$19.00	MIV175	\$5.25
ULPCM175150T	\$83.00	ULPCM175150G	\$81.00	7.09 x 7.09 x 5.98 [180 x 180 x 152]	4.02 [102]	PDF	FPA175180	\$19.00	MIV175	\$5.25
ULPCM20063T	\$121.00	ULPCM20063G	\$120.00	10.04 x 7.09 x 2.48 [255 x 180 x 63]	0.51 [13]	PDF	FPA200180	\$24.50	MIV200	\$7.25
ULPCM20075T	\$122.00	ULPCM20075G	\$121.00	10.04 x 7.09 x 3.03 [255 x 180 x 77]	1.06 [27]	PDF	FPA200180	\$24.50	MIV200	\$7.25
ULPCM200100T	\$123.00	ULPCM200100G	\$121.00	10.04 x 7.09 x 4.02 [255 x 180 x 102]	2.05 [52]	PDF	FPA200180	\$24.50	MIV200	\$7.25
ULPCM200150T	\$129.00	ULPCM200150G	\$126.00	10.04 x 7.09 x 5.98 [255 x 180 x 152]	4.02 [102]	PDF	FPA200180	\$24.50	MIV200	\$7.25

Note: Dimensions in inches [millimeters].

*FPA175180 requires hinge HFP180 to mount

www.automationdirect.com

MNX Series Polycarbonate Miniature Cases, Tall Base

MNX Series Polycarbonate Miniature Cases with Knockouts, Tall Base										
Smoked Cover	Price	Solid Cover	Price	Enclosure Size HxWxD	Cover Depth	Drawing Link	Front Swing Panel*	Price	Subpanel	Price
ULPCM15085XT	\$61.00	ULPCM15085XG	\$61.00	7.09 x 5.12 x 3.39 [180 x 130 x 86]	0.43 [11]	PDF	—	—	MIV150	\$4.50
ULPCM150100XT	\$61.00	ULPCM150100XG	\$61.00	7.09 x 5.12 x 4.02 [180 x 130 x 102]	1.06 [27]	PDF	—	—	MIV150	\$4.50
ULPCM150125XT	\$62.00	ULPCM150125XG	\$62.00	7.09 x 5.12 x 5.00 [180 x 130 x 127]	2.05 [52]	PDF	—	—	MIV150	\$4.50
ULPCM150150XT	\$64.00	ULPCM150150XG	\$64.00	7.09 x 5.12 x 5.98 [180 x 130 x 152]	3.03 [77]	PDF	—	—	MIV150	\$4.50
ULPCM150175XT	\$66.00	ULPCM150175XG	\$66.00	7.09 x 5.12 x 6.97 [180 x 130 x 177]	4.02 [102]	PDF	—	—	MIV150	\$4.50
ULPCM17585XT	\$103.00	ULPCM17585XG	\$103.00	7.09 x 7.09 x 3.35 [180 x 180 x 85]	0.43 [11]	PDF	FPA175180	\$19.00	MIV175	\$5.25
ULPCM175100XT	\$100.00	—	\$100.00	7.09 x 7.09 x 3.98 [180 x 180 x 101]	1.06 [27]	PDF	FPA175180	\$19.00	MIV175	\$5.25
ULPCM175125XT	\$100.00	ULPCM175125XG	\$100.00	7.09 x 7.09 x 4.96 [180 x 180 x 126]	2.05 [52]	PDF	FPA175180	\$19.00	MIV175	\$5.25
ULPCM175150XT	\$103.00	ULPCM175150XG	\$103.00	7.09 x 7.09 x 5.94 [180 x 180 x 151]	3.03 [77]	PDF	FPA175180	\$19.00	MIV175	\$5.25
ULPCM175175XT	\$106.00	ULPCM175175XG	\$106.00	7.09 x 7.09 x 6.93 [180 x 180 x 176]	4.02 [102]	PDF	FPA175180	\$19.00	MIV175	\$5.25
ULPCM20088XT	\$127.00	ULPCM20088XG	\$127.00	10.04 x 7.09 x 3.46 [255 x 180 x 88]	0.51 [13]	PDF	FPA200180	\$24.50	MIV200	\$7.25
ULPCM200100XT	\$128.00	ULPCM200100XG	\$128.00	10.04 x 7.09 x 4.02 [255 x 180 x 102]	1.06 [27]	PDF	FPA200180	\$24.50	MIV200	\$7.25
ULPCM200125XT	\$129.00	ULPCM200125XG	\$129.00	10.04 x 7.09 x 5.00 [255 x 180 x 127]	2.05 [52]	PDF	FPA200180	\$24.50	MIV200	\$7.25
ULPCM200175XT	\$135.00	ULPCM200175XG	\$135.00	10.04 x 7.09 x 6.97 [255 x 180 x 177]	4.02 [102]	PDF	FPA200180	\$24.50	MIV200	\$7.25

Note: Dimensions in inches [millimeters].

*FPA175180 requires hinge HFP180 to mount

MNX Series Accessories

Cover Screws				
Part Number	Price	Description	Photo	Drawing Link
<u>MBSHH</u>	\$5.00	Fibox cover screw, replacement, Phillips pan head, polyamide and steel. Package of 4. For use with MNX lid depth more than 25 mm and TEMPO enclosures less than 200 mm high.		<u>PDF</u>

Mounting Feet Kit				
Part Number	Price	Description	Photo	Drawing Link
<u>FP10674</u>	\$3.75	Fibox mounting feet, polycarbonate, RAL 7035 light gray. For use with TEMPO series enclosures. (2) mounting feet and hardware included.		<u>PDF</u>
<u>FP22046</u>	\$2.75	Fibox mounting feet, polycarbonate, RAL 7035 light gray. For use with MNX series enclosures. (4) mounting feet and hardware included.		<u>PDF</u>

Swing Panel Hinge				
Part Number	Price	Description	Photo	Drawing Link
<u>HFP180</u>	\$5.50	Fibox swing panel bracket, polycarbonate. For use with swing panels FPAxxx180. Hinge and hardware included.		<u>PDF</u>

**MIV15**

MNX DIN Rail				
Part Number	Price	Length	For use with	Drawing Link
<u>MIV5</u>	\$3.50	1.97 in	ULPCM100xxx MNX series enclosures	<u>PDF</u>
<u>MIV10</u>	\$4.25	3.94 in	ULPCM100xxx ULPCM125xxx and ULPCM150xxxMNX series enclosures	<u>PDF</u>
<u>MIV15</u>	\$5.00	5.91 in	ULPCM150xxx ULPCM175xxx and ULPCM200xxxMNX series enclosures	<u>PDF</u>
<u>MIV20</u>	\$5.50	8.86 in	ULPCM200xxxMNX series enclosures	<u>PDF</u>