

# Enclosure Accessories Deep-Hinged Door with Window



## Application

- Extra deep kits are designed to provide protection and easy access to components and equipment installed inside an enclosure.
- Maintain environmental protection level of NEMA 4 and 12 (NEMA 4X for stainless steel).
- Frame is 1/4 gauge mild steel or 316L stainless steel.
- 1/4-turn latch for easy access.
- 2.5in of extra usable depth.
- Oil-resistant neoprene gasket ensures a watertight seal.
- Can be either left- or right-hand hinged.
- Window is 0.25in thick, UV-Resistant Polycarbonate.
- Conveniently sized to allow mounting on the door of any Hammond wallmount enclosure or in any other Hammond enclosure with a suitable mounting surface.
- Mounting hardware and template are included.
- Finished in ANSI 61 gray recoatable powder or #4 brushed stainless steel.

Shipping Schedule	
Same day	1 - 15 days
Color indicates shipping lead time in business days.	

Deep-Hinged Windows								
Carbon Steel	Price	Stainless Steel	Price	Drawing Link	Overall Dimensions HxWxD	Viewing Area YxZ	# of Latches	Maximum Cut-Out Size
<b>1481WDH1418</b>	\$421.00	<b>1481WSSDH1418</b>	\$1,031.00	PDF	12.19 x 14.56 x 2.75in [309 x 370 x 70]	8.00 x 9.17in [203 x 233]	1	9.19 x 11.56in [233 x 297]
<b>1481WDH1612</b>	\$444.00	<b>1481WSSDH1612</b>	\$1,086.00	PDF	14.19 x 8.14 x 2.75in [360 x 207 x 70]	10.00 x 2.75in [254 x 70]	1	11.19 x 5.14in [284 x 131]
<b>1481WDH1620</b>	\$531.00	—	—	PDF	14.19 x 16.14 x 2.75 [360 x 410 x 70]	10.00 x 10.75 [254 x 273 x 0]	1	11.19 x 13.14 [284 x 334 x 0]
<b>1481WDH1624</b>	\$570.00	—	—	PDF	14.19 x 20.14 x 2.75 [360 x 512 x 70]	10.00 x 14.75 [254 x 375 x 0]	1	11.19 x 17.14 [284 x 435 x 0]
<b>1481WDH2016</b>	\$531.00	<b>1481WSSDH2016</b>	\$1,299.00	PDF	18.19 x 12.14 x 2.75in [462 x 308 x 70]	14.00 x 6.75in [356 x 171]	1	15.19 x 9.14in [386 x 232]
<b>1481WDH2024</b>	\$610.00	—	—	PDF	18.19 x 20.14 x 2.75 [462 x 512 x 70]	14.00 x 14.75 [356 x 375 x 0]	1	15.19 x 17.14 [386 x 435 x 0]
<b>1481WDH2416</b>	\$570.00	<b>1481WSSDH2416</b>	\$1,393.00	PDF	22.19 x 12.14 x 2.75in [564 x 308 x 70]	18.00 x 6.75in [457 x 171]	1	19.19 x 9.14in [487 x 232]
<b>1481WDH2420</b>	\$610.00	<b>1481WSSDH2420</b>	\$1,491.00	PDF	22.19 x 16.14 x 2.75in [564 x 410 x 70]	18.00 x 10.75in [457 x 273]	1	19.19 x 13.14in [487 x 334]
<b>1481WDH2430</b>	\$729.00	<b>1481WSSDH2430</b>	\$1,779.00	PDF	22.19 x 26.14 x 2.75in [564 x 664 x 70]	18.00 x 20.75in [457 x 527]	1	19.19 x 23.14in [487 x 588]
<b>1481WDH3024</b>	\$729.00	<b>1481WSSDH3024</b>	\$1,779.00	PDF	28.19 x 20.14 x 2.75in [716 x 512 x 70]	24.00 x 14.75in [610 x 375]	2	25.19 x 17.14in [640 x 435]
<b>1481WDH3624</b>	\$848.00	<b>1481WSSDH3624</b>	\$2,067.00	PDF	34.19 x 20.14 x 2.75in [868 x 512 x 70]	30.00 x 14.75in [762 x 375]	2	31.19 x 17.14in [792 x 435]

Note: Dimensions in inches [millimeters].

