

# Enclosure Accessories



## Drip Shield Kit



## Application

- Easily installed on NEMA 12, 4, and 4X wall-mount enclosures using stainless steel bolts and sealing washers (included).
- Designed not to interfere with door clamps.
- Protects door from dripping water and settling dust.
- Constructed in 14-gauge mild steel (painted) or 316 stainless steel.
- Maintains enclosure rating.

Drip Shield Kit - DK Series							
ANSI 61 Gray	Price	RAL7035 Lt Gray	Price	Stainless Steel	Price	Fits Enclosure Width (in.)	Drawing Link
<a href="#">DK12GY</a>	\$62.00	<a href="#">DK12LG</a>	\$62.00	<a href="#">DK12S16</a>	\$113.00	12.0 [305]	<a href="#">PDF</a>
<a href="#">DK16GY</a>	\$68.00	<a href="#">DK16LG</a>	\$68.00	<a href="#">DK16S16</a>	\$123.00	16.0 [406]	<a href="#">PDF</a>
<a href="#">DK20GY</a>	\$74.00	<a href="#">DK20LG</a>	\$74.00	<a href="#">DK20S16</a>	\$134.00	20.0 [508]	<a href="#">PDF</a>
<a href="#">DK24GY</a>	\$81.00	<a href="#">DK24LG</a>	\$81.00	<a href="#">DK24S16</a>	\$144.00	24.0 [610]	<a href="#">PDF</a>
<a href="#">DK30GY</a>	\$91.00	<a href="#">DK30LG</a>	\$91.00	<a href="#">DK30S16</a>	\$161.00	30.0 [762]	<a href="#">PDF</a>
<a href="#">DK36GY</a>	\$99.00	<a href="#">DK36LG</a>	\$99.00	<a href="#">DK36S16</a>	\$176.00	36.0 [914]	<a href="#">PDF</a>
<a href="#">DK42GY</a>	\$110.00	<a href="#">DK42LG</a>	\$110.00	<a href="#">DK42S16</a>	\$187.00	42.0 [1067]	<a href="#">PDF</a>
<a href="#">DK48GY</a>	\$118.00	<a href="#">DK48LG</a>	\$118.00	<a href="#">DK48S16</a>	\$197.00	48.0 [1219]	<a href="#">PDF</a>
<a href="#">DK60GY</a>	\$136.00	<a href="#">DK60LG</a>	\$136.00	<a href="#">DK60S16</a>	\$230.00	60.0 [1524]	<a href="#">PDF</a>
<a href="#">DK72GY</a>	\$153.00	—	—	<a href="#">DK72S16</a>	\$256.00	72.0 [1829]	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].

## Pedestal Columns and Bases for Operator Consoles



Pedestal Column



Pedestal Base

## Application

- Used for floor-mounting many types of enclosures, consolets or pushbutton boxes.
- Provides wiring feature through the column.

## Pedestal Column

- Columns are formed from 14-gauge steel with 10-gauge flanges.
- Column access opening with gasketed cover.
- Columns include flange gaskets and a box connector.

## Pedestal Base

- Bases are formed from 10-gauge steel with additional reinforcing.

Pedestal Columns and Bases for Operator Consoles			
Part Number	Price	Description	Drawing Link
<a href="#">1495C35</a>	\$314.00	Straight pedestal column, carbon steel, 35.00 x 4.00 x 4.00in, ANSI 61 gray, powder coat finish. For use with operator consolets. Flange gaskets, box connector and mounting hardware included.	<a href="#">PDF</a>
<a href="#">1495D35</a>	\$470.00	Straight pedestal column, carbon steel, 35.00 x 6.00 x 6.00in, ANSI 61 gray, powder coat finish. For use with operator consolets. Flange gaskets, box connector and mounting hardware included.	<a href="#">PDF</a>
<a href="#">1495XK</a>	\$195.00	Pedestal base, carbon steel, 18.00 x 18.00in, ANSI 61 gray, powder coat finish. For use with pedestal columns. Leveling screws included.	<a href="#">PDF</a>
<a href="#">1495XN</a>	\$433.00	Pedestal base, carbon steel, 24.00 x 24.00in, ANSI 61 gray, powder coat finish. For use with pedestal columns. Leveling screws included.	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].