

Enclosure Accessories

Hole Seals and Plugs



Carbon Steel



Stainless Steel

Features

- Designed to seal unused pushbutton holes, conduit openings and knockout holes against dust, oil, and water.
- Available in carbon with ANSI gray finish and 304 stainless steel with #4 brushed finish.
- Oil-resistant gasket.
- Secured with an 10-24 x 0.55in [14 mm] threaded stud and plated wing nut.

Hole Seals						
Carbon Steel	Price	Stainless Steel	Price	Max Hole Diameter	Overall Seal Diameter	Drawing Link
HP22	\$6.50	HP22SS	\$16.50	0.88 [22]	1.22 [31]	PDF
HP50	\$6.50	HP50SS	\$16.50	0.88 [22]	1.38 [35]	PDF
HP75	\$8.25	HP75SS	\$21.00	1.06 [27]	1.56 [40]	PDF
HPB	\$8.75	HPBSS	\$23.50	1.25 [32]	1.75 [44]	PDF
HP100	\$11.25	HP100SS	\$28.50	1.38 [35]	1.88 [48]	PDF
HP125	\$12.50	HP125SS	\$32.50	1.69 [43]	2.19 [56]	PDF
HP150	\$14.25	HP150SS	\$37.00	2.00 [51]	2.50 [64]	PDF
HP200	\$15.75	HP200SS	\$41.00	2.50 [64]	3.00 [76]	PDF
HP250	\$20.00	—	—	3.00 [76]	3.50 [89]	PDF
HP350	\$34.50	—	—	4.12 [92]	4.12 [105]	PDF
HP300	\$26.50	—	—	3.62 [105]	4.62 [117]	PDF
HP400	\$44.00	—	—	4.62 [117]	5.12 [130]	PDF

Note: Dimensions in inches [millimeters].