

Enclosure Accessories

NEMA 3R Louvered Vent Kits



Application

- Provides ventilation in enclosures for either Indoor or outdoor locations.
- Gasketed sealing kit provides protection to NEMA 3R.
- Aluminum filter mesh provides ingress protection for both solid debris and outdoor rain conditions.
- Easily field install kit includes all hardware.
- Louver plates are offered in both 14 gauge steel with ANSI 61 gray powder coat finish or 304 stainless steel.

Shipping Schedule

Same day	1 - 15 days
----------	-------------

Color indicates shipping lead time in business days.

NEMA 3R Louvered Vent Kits							
ANSI 61 Gray	Price	Stainless Steel	Price	Overall Size	Cutout Size	# Louvers	Louver Length
1481L3R55GY	\$40.50	1481L3R55SS	\$98.00	5.56 x 5.30in (HxW)	3.00 x 2.75in (HxW)	3	3.00in
1481L3R56GY	\$42.00	1481L3R56SS	\$104.00	5.30 x 6.30in (HxW)	2.88 x 3.75in (HxW)	3	4.00in
1481L3R66GY	\$43.50	1481L3R66SS	\$110.00	6.40 x 6.30in (HxW)	4.00 x 3.75in (HxW)	4	4.00in
1481L3R68GY	\$47.00	—	—	6.40 x 8.30in (HxW)	3.50 x 5.75in (HxW)	4	6.00in
1481L3R88GY	\$50.00	—	—	8.69 x 8.30in (HxW)	5.75 x 5.75in (HxW)	6	6.00in
1481L3R610GY	\$52.00	—	—	6.62 x 10.30in (HxW)	3.75 x 7.75in (HxW)	4	8.00in
1481L3R810GY	\$56.00	—	—	9.00 x 10.30in (HxW)	6.25 x 7.75in (HxW)	6	8.00in
1481L3R1110GY	\$60.00	—	—	11.37 x 10.30in (HxW)	8.50 x 7.75in (HxW)	8	8.00in
1481L3R1510GY	\$66.00	—	—	16.12 x 10.30in (HxW)	13.25 x 7.75in (HxW)	9	8.00in

Replacement Aluminum Filter Mats for Louvered Vent Kits

Replacement Aluminum Filter Mats for Louvered Vent Kits		
Part Number	Price	Size HxW
LFK55	\$22.00	3.15 x 3.00in (HxW)
LFK56	\$22.50	3.25 x 4.00in (HxW)
LFK66	\$23.00	4.38 x 4.00in (HxW)
LFK68	\$24.50	4.38 x 6.00in (HxW)
LFK88	\$25.00	6.63 x 6.00in (HxW)
LFK610	\$28.00	4.56 x 8.00in (HxW)
LFK810	\$29.00	6.94 x 8.00in (HxW)
LFK1110	\$29.50	9.31 x 8.00in (HxW)
LFK1510	\$29.50	14.06 x 8.00in (HxW)



Enclosure Accessories

NEMA 1 Louvered Ventilating Plates



Application

- Provides ventilation in enclosures where required.
- Easily installed in the field by cutting a square hole of the proper size and bolting the ventilator in place.
- Finished in gray.
- Hole diameter is 0.22in.

Shipping Schedule	
Same day	1 - 15 days
Color indicates shipping lead time in business days.	

NEMA 1 Louvered Ventilating Plates						
Part Number	Price	Overall Size	Opening Area (in ²)	# Rows	# Louvers	Louver Length
1481L44	\$21.00	5.62 x 5.50in (HxW)	4.5	1	4	4.00in
1481L66	\$25.00	7.87 x 7.50in (HxW)	5.3	2	14	2.00in
1481L88	\$30.50	10.56 x 10.50in (HxW)	20.2	2	18	4.00in

Pressure Compensation Plug

Application

- Packaged individually.
- Provides for controlled pressure compensation due to temperature variations (i.e. night/day operation).
- When mounted to bottom of enclosure, this unique design provides a method of effectively draining moisture from within the enclosure
- Recommend two plugs per cabinet in opposite locations.
- Pipe Thread 1/2in NPT (actual dia. 0.813in)
- Recommended Torque 10 NM



Pressure Compensation Plug	
Part Number	Price
BDN4XN1	\$38.50

Enclosure Accessories



Small Rainproof Ventilator



Application

- Designed to equalize internal / external pressure and temperature.
- Ventilators assist in condensation prevention by allowing enclosures to breathe.
- Suitable for most types of metallic and non-metallic enclosures.
- Molded in corrosion-resistant UV stabilized polycarbonate, finish RAL7035 Light Gray.
- Gasket protection to enclosure wall.
- Approximately 1.18in [30mm] high x 0.98in [25mm] wide.
- Mount to enclosure wall thickness up to .16in [4mm].
- Internal vent channel and grille reduces insect intrusion.
- Complies with NEMA Type 3R, IEC 60529 IP24.

Shipping Schedule	
Same day	1 - 15 days
Color indicates shipping lead time in business days.	

Small Rainproof Ventilator	
Part Number	Price
SDV180-1	\$4.50

Large Rainproof Ventilator



Application

- Designed to equalize internal / external pressure and temperature.
- Ventilators assist in condensation prevention by allowing enclosures to breathe.
- Suitable for most types of metallic and non-metallic enclosures.
- Molded in corrosion-resistant UV stabilized polycarbonate, finish RAL7035 Light Gray.
- Gasket protection to enclosure wall.
- Approximately 2.73in [69mm] high x 1.99in [51mm] wide.
- Mount to enclosure wall thickness up to .16in [4mm] with standard screws.
- Internal vent channel and grille reduces insect intrusion.
- Complies with NEMA Type 3R, IEC 60529 IP24.

Large Rainproof Ventilator	
Part Number	Price
SDV280-1	\$8.00