

Enclosure Deep-Hinged Doors



Features

- Extra deep kits are designed to provide protection and easy access to components and equipment installed inside an enclosure.
- Frame is 14-gauge carbon steel or 316L stainless steel.
- Maintain environmental protection level of enclosure. Painted mild steel maintain Type 4 and 12. Stainless Steel maintain Type 4, 4X, and 12.
- 1/4 turn latch for easy access.
- 2.5 in [64 mm] [63.5 mm] of extra usable depth.
- Oil resistant neoprene gasket ensures a watertight seal.
- Hinges can be oriented in any direction.
- Conveniently sized to allow mounting on any enclosure with a suitable mounting surface.
- Mounting hardware and template are included.
- Finished in ANSI 61 gray recoatable powder or natural #4 brushed stainless steel.

Listings

- UL Type 4, 4X (Stainless Steel Only) and 12 [UL file E65324]
- CSA Type 4, 4X (Stainless Steel Only) and 12 [CSA file LL21312]
- NEMA Type 4, 4X, and 12



Deep-Hinged Doors						
Part Number Carbon Steel	Price	Part Number Stainless Steel	Price	Drawing Link	Overall Dimensions HxWxD	Maximum Cut-Out Size
1481SDH1418	\$439.00	1481SSDH1418	\$1,042.00	PDF	12.19 x 14.56 x 2.75 [310 x 370 x 70]	9.19 x 11.56 [233 x 294]
1481SDH1612	\$462.00	1481SSDH1612	\$1,097.00	PDF	14.19 x 8.14 x 2.75 [360 x 207 x 70]	11.19 x 5.14 [284 x 131]
1481SDH1620	\$552.00	1481SSDH1620	\$1,312.00	PDF	14.19 x 16.14 x 2.75 [360 x 410 x 70]	11.19 x 13.14 [284 x 334]
1481SDH2016	\$552.00	1481SSDH2016	\$1,312.00	PDF	18.19 x 12.14 x 2.75 [462 x 308 x 70]	15.19 x 9.14 [386 x 232]
1481SDH1624	\$593.00	1481SSDH1624	\$1,408.00	PDF	14.19 x 20.14 x 2.75 [360 x 512 x 70]	11.19 x 17.14 [284 x 435]
1481SDH2416	\$593.00	1481SSDH2416	\$1,408.00	PDF	22.19 x 12.14 x 2.75 [564 x 308 x 70]	19.19 x 9.14 [487 x 232]
1481SDH2024	\$635.00	1481SSDH2024	\$1,507.00	PDF	18.19 x 20.14 x 2.75 [462 x 512 x 70]	15.19 x 17.14 [386 x 435]
1481SDH2420	\$635.00	1481SSDH2420	\$1,507.00	PDF	22.19 x 16.14 x 2.75 [564 x 410 x 70]	19.19 x 13.14 [487 x 334]
1481SDH2430	\$759.00	1481SSDH2430	\$1,798.00	PDF	22.19 x 26.14 x 2.75 [564 x 664 x 70]	19.19 x 23.14 [487 x 588]
1481SDH3024	\$759.00	1481SSDH3024	\$1,798.00	PDF	28.19 x 20.14 x 2.75 [716 x 512 x 70]	25.19 x 17.14 [640 x 435]
1481SDH3624	\$883.00	1481SSDH3624	\$2,089.00	PDF	34.19 x 20.14 x 2.75 [868 x 512 x 70]	31.19 x 17.14 [792 x 435]

Note: Dimensions in inches [millimeters].

