

# Enclosure Accessories

## Frameless Window Kits



### Application

- Designed for indoor use on NEMA 12 and 13 enclosures.
- Scratch-resistant polycarbonate window is 0.25in [6.35mm] thick.
- Double-sided tape is on the window for easy installation.
- Mounting hardware and template are included.

Frameless Window Kits				
Part Number	Price	Window Dimensions AxB	Maximum Cut-Out Size	Drawing Link
<a href="#">1481WFL52</a>	\$59.00	5.50 x 3.00 [140 x 76]	4.50 x 2.00 [114 x 51]	<a href="#">PDF</a>
<a href="#">1481WFL133</a>	\$73.00	13.88 x 3.88 [353 x 99]	12.88 x 2.88 [327 x 73]	<a href="#">PDF</a>
<a href="#">1481WFL96</a>	\$81.00	9.62 x 7.19 [244 x 183]	8.62 x 6.19 [219 x 157]	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].

