

NEMA 12 Wiring Trough



Listings

- UL 870 Type 1
- CSA Type 1
- Complies with:
 - NEMA Type 12
 - IEC 60529, IP54



Designed to enclose and protect multiple wiring junctions from dirt, dust, oil and water.

Construction

- Formed 14-gauge steel.
- Smooth continuously welded seams.
- Butt-hinged cover is secured with easily operated screw clamps.
- Oil resistant gaskets are permanently secured.
- 12-gauge external mounting feet are welded to the back.
- Troughs and covers are finished in ANSI 61 gray powder coating.



Shipping Schedule

Same day 1 - 15 days

Color indicates shipping lead time in business days.

NEMA 12 Wiring Trough

Part Number	Price	Overall Size HxWxD	Drawing Link
1486B12	\$106.00	2.50 x 2.50 x 12.00 [64 x 64 x 305]	PDF
1486B18	\$114.00	2.50 x 2.50 x 18.00 [64 x 64 x 457]	PDF
1486B24	\$123.00	2.50 x 2.50 x 24.00 [64 x 64 x 610]	PDF
1486B30	\$132.00	2.50 x 2.50 x 30.00 [64 x 64 x 762]	PDF
1486B36	\$139.00	2.50 x 2.50 x 36.00 [64 x 64 x 914]	PDF
1486B48	\$156.00	2.50 x 2.50 x 48.00 [64 x 64 x 1219]	PDF
1486B60	\$173.00	2.50 x 2.50 x 60.00 [64 x 64 x 1524]	PDF
1486B72	\$188.00	2.50 x 2.50 x 72.00 [64 x 64 x 1829]	PDF
1486C12	\$124.00	4.00 x 4.00 x 12.00 [102 x 102 x 305]	PDF
1486C18	\$139.00	4.00 x 4.00 x 18.00 [102 x 102 x 457]	PDF
1486C24	\$156.00	4.00 x 4.00 x 24.00 [102 x 102 x 610]	PDF
1486C30	\$172.00	4.00 x 4.00 x 30.00 [102 x 102 x 762]	PDF
1486C36	\$186.00	4.00 x 4.00 x 36.00 [102 x 102 x 914]	PDF
1486C48	\$225.00	4.00 x 4.00 x 48.00 [102 x 102 x 1219]	PDF
1486C60	\$257.00	4.00 x 4.00 x 60.00 [102 x 102 x 1524]	PDF
1486C72	\$281.00	4.00 x 4.00 x 72.00 [102 x 102 x 1829]	PDF
1486D12	\$147.00	6.00 x 6.00 x 12.00 [152 x 152 x 305]	PDF
1486D18	\$170.00	6.00 x 6.00 x 18.00 [152 x 152 x 457]	PDF
1486D24	\$194.00	6.00 x 6.00 x 24.00 [152 x 152 x 610]	PDF
1486D30	\$216.00	6.00 x 6.00 x 30.00 [152 x 152 x 762]	PDF
1486D36	\$240.00	6.00 x 6.00 x 36.00 [152 x 152 x 914]	PDF
1486D48	\$287.00	6.00 x 6.00 x 48.00 [152 x 152 x 1219]	PDF
1486D60	\$345.00	6.00 x 6.00 x 60.00 [152 x 152 x 1524]	PDF
1486D72	\$393.00	6.00 x 6.00 x 72.00 [152 x 152 x 1829]	PDF

Note: Dimensions in inches [millimeters].