

Two-Post Heavy-Duty Battery Shelf



Features

- Designed for use with our Heavy-Duty DNRR and DRZ4 double-tapped two-post racks.
- Constructed of heavy-duty 12-gauge steel.
- Use to support heavy chassis or batteries for DC battery array.
- Choice of 19 in [483 mm] or 24 in [610 mm] deep.
- Front and rear lip folded and welded for extra strength and retention.
- For a similar design that is light duty and vented, see the DNRM Series.
- Finished in a rugged textured black powder coat finish.
- Tested to nearly double the suggested load rating of 550 lb [250 kg].

Listings

- TAA compliant for GSA Schedule purchases.

Two-Post Heavy-Duty Battery Shelf				
Part Number	Price	Rack Units	Rack Width	Drawing Link
BRS2P1919BK	\$129.00	3U	19.0 [483]	PDF
BRS2P1924BK	\$146.00	3U	19.0 [483]	PDF
BRS2P2319BK	\$137.00	3U	23.0 [584]	PDF
BRS2P2324BK	\$155.00	3U	23.0 [584]	PDF

Note: Dimensions in inches [millimeters].