

2-Post Open Frame 19-Inch & 23-Inch Welded Rack



Features

- Automated tapping process provides threaded rails on both the front and back to ensure flexibility when mounting equipment.
 - Includes marked rack unit dividers to aid in equipment mounting.
- For connecting multiple racks together: numerous holes for mounting power distribution, cable management and other accessories are provided.
- Bonding is possible two pairs of integrated 10-32 ground studs, spaced 0.63in [16mm] apart. Stud pairs are conveniently located across from each other inside the rail channel. For added convenience, a pair of studs is located near the top of the rack, while another pair is located at the lower side.

Construction

- 10-gauge steel
- Three-stage paint process which includes a coat of premium smooth black powder coat.
- In order to prevent any damage that may occur during transportation, rails and base are protected with a thick layer of cardboard.
- UL Listed 2416 load rated for up to 1,500lb [680kg]. Static Load tested to 6,000lb [2,721kg].

Listings

- TAA compliant for GSA Schedule purchases.
- EIA compliant
- RoHS
- cULus File E474597



Shipping Schedule

Same day	1 - 15 days
----------	-------------

Color indicates shipping lead time in business days.

2-Post Open Frame 19-Inch Knockdown Rack

Part Number	Price	Rack Units	Rack Width	Drawing Link
DNRR63HDW	\$426.00	36U	19in	PDF
DNRR70HDW	\$324.00	40U		PDF
DNRR77HDW	\$460.00	44U		PDF
DNRR84HDW	\$502.00	48U		PDF
DNRR2377HDWB	\$439.00	44U	23in	PDF
DNRR2384HDWB	\$466.00	48U		PDF