


# Adjustable Depth Hinged Wall-Mount 19-Inch Rack



## Features

- Available in 4U, 6U, 8U and 12U mounting heights.
- Hinged for easy rear access.
- Adjusts in depth from 12in to 18in with ease so there is no need to disassemble the wholerack to adjust the depth.
- Rear cable access with multiple tie points for cable management.
- Knockdown design ships unassembled for easy handling, reduced freight cost and shipping protection.

## Construction

- Constructed from 14-gauge steel.
- Tapped 10-32 19in mounting rails are constructed from 14-gauge steel and include rack unit indicators.
- SCREW1032-25, 25-pack of 10-32 mounting hardware included.
- Load rated for up to 100lb [45kg].
- Finished in smooth black powder coat.

## Listings

- TAA compliant for GSA Schedule purchases.
- RoHS



### Shipping Schedule

Same day	1 - 15 days
----------	-------------

Color indicates shipping lead time in business days.

### Adjustable Depth Hinged Wall-Mount 19-Inch Rack

Part Number	Rack Units	Price	Drawing Link
<a href="#">APB19007BK1</a>	4U	\$89.00	<a href="#">PDF</a>
<a href="#">APB19010BK1</a>	6U	\$97.00	<a href="#">PDF</a>
<a href="#">APB19014BK1</a>	8U	\$105.00	<a href="#">PDF</a>
<a href="#">APB19021BK1</a>	12U	\$140.00	<a href="#">PDF</a>