

# Adjustable Depth Wall-Mount 19-Inch Rack with Shelf



## Features

- Available in 4U and 8U mounting heights.
  - Includes 3.5 in [89mm] (2U) of space for non-rack mounting equipment.
- Includes twelve 12in deep accessory shelf.
- Depth is adjustable from 12in to 18in with ease so there is no need to disassemble the wholerack to adjust the depth.
- Rear cable access with multiple tie points for cable management.
- Knockdown design ships unassembled for easy handling, reduced freight cost and shipping protection.

## Construction

- Constructed from 14-gauge steel.
- Tapped 10-32 19in mounting rails are constructed from 14-gauge steel and include rack unit indicators.
- SCREW1032-25, 25-pack of 10-32 mounting hardware included.
- Load rated for up to 100lb [45kg].
- Finished in smooth black powder coat.

## Listings

- TAA compliant for GSA Schedule purchases.
- RoHS



Shipping Schedule	
Same day	1 - 15 days
Color indicates shipping lead time in business days.	

Adjustable Depth Wall-Mount 19-Inch Rack with Shelf			
Part Number	Price	Rack Units	Drawing Link
<a href="#">APBS194UBK</a>	\$117.00	4U	<a href="#">PDF</a>
<a href="#">APBS198UBK</a>	\$154.00	8U	<a href="#">PDF</a>