

NEMA 4, 4X, 6, & 6P Polycarbonate Flanged Miniature Cases with Styled Lid



Features

- Ideally suited for mounting printed circuit boards.
- Can be used in a tabletop configuration or two different wall-mount configurations.
- Rounded corners and face provide a more modern look while still offering superior watertight ratings.
 - ABS plastic or ABS Versions are molded from general purpose material which carries a flammability rating of UL94-HB. For indoor use.
- Gasketed lid with two piece tongue & groove construction provides protection against oil, dust, and water.
- Lid is secured with included M4 stainless steel machine screws which are threaded into integral stainless steel bushings for repetitive assembly & disassembly. All hardware is stainless steel to avoid corrosion.
- Foot Kits available: (1557FOOT2BK-24, 1557FOOT2GY-24, 1557FOOTBK-24, 1557FOOTGY-24)

Materials

- Available in black or gray
- UL listed polycarbonate
- Gasket is one piece made from high temperature, UL listed silicone.
 - Sold in pairs

Listings

- UL94-HB for indoor or outdoor use
 - UL 508A Type 4, 4X, 6, & 6P
 - [UL File E63524]
- Complies with
 - NEMA 4, 4X, 6, & 6P
 - IEC 60529, IP68



Enclosure Shipping Schedule	
Same day	1 - 15 days
Color indicates shipping lead time in business days.	

NEMA 4, 4X, 6, & 6P Polycarbonate Miniature Cases							
Part Number		Price	Enclosure Size HxWxD	Lid Depth	Drawing Link	Replacement Gasket	Price
Black	Light Gray						
1557B2BK	1557B2GY	\$12.75	3.15 x 3.15 x 1.77 [80 x 80 x 45]	30mm	PDF	1557BGASKET	\$4.50
1557BA2BK	1557BA2GY	\$13.25	3.15 x 3.15 x 2.36 [80 x 80 x 60]	45mm	PDF	1557BGASKET	\$4.50
1557D2BK	1557D2GY	\$14.75	4.72 x 4.72 x 1.77 [120 x 120 x 45]	31mm	PDF	1557DGASKET	\$4.50
1557DA2BK	1557DA2GY	\$17.25	4.72 x 4.72 x 2.76 [120 x 120 x 70]	56mm	PDF	1557DGASKET	\$4.50
1557F2BK	1557F2GY	\$21.00	6.30 x 6.30 x 1.77 [160 x 160 x 45]	31mm	PDF	1557FGASKET	\$8.50
1557FA2BK	1557FA2GY	\$26.50	6.30 x 6.30 x 2.76 [160 x 160 x 70]	56mm	PDF	1557FGASKET	\$8.50
1557H2BK	1557H2GY	\$26.50	7.87 x 7.87 x 1.77 [200 x 200 x 45]	31mm	PDF	1557HGASKET	\$8.75
1557HA2BK	1557HA2GY	\$29.50	7.87 x 7.87 x 2.76 [200 x 200 x 70]	56mm	PDF	1557HGASKET	\$8.75

Notes: Dimensions in inches [millimeters].

IP66 ABS Plastic Flanged Miniature Cases with Styled Lid



Features

- Ideally suited for mounting printed circuit boards.
- Can be used in a tabletop configuration or two different wall-mount configurations.
- Rounded corners and face provide a more modern look while still offering superior watertight ratings.
 - ABS plastic or ABS Versions are molded from general purpose material which carries a flammability rating of UL94-HB. For indoor use.
- Gasketed lid with two piece tongue & groove construction provides protection against oil, dust, and water.
- Lid is secured with included M4 stainless steel machine screws which are threaded into integral stainless steel bushings for repetitive assembly & disassembly. All hardware is stainless steel to avoid corrosion.
- Foot Kits available: (1557FOOT2BK-24, 1557FOOT2GY-24, 1557FOOTBK-24, 1557FOOTGY-24)



Materials

- Available in black or gray.
- General Purpose ABS plastic
- Gasket is one piece made from high temperature, UL listed silicone.
 - Sold in pairs

Listings

- Complies with IEC 60529, IP66



Enclosure Shipping Schedule	
Same day	1 - 15 days
Color indicates shipping lead time in business days.	

IP66 ABS Plastic Miniature Cases							
Part Number		Price	Enclosure Size HxWxD	Lid Depth	Drawing Link	Replacement Gasket	Price
Black	Light Gray						
1557BABK	1557BAGY	\$10.00	3.15 x 3.15 x 2.36 [80 x 80 x 60]	45mm	PDF	1557BGASKET	\$4.50
1557BBK	1557BGY	\$9.75	3.15 x 3.15 x 1.77 [80 x 80 x 45]	30mm	PDF	1557BGASKET	\$4.50
1557DABK	1557DAGY	\$14.75	4.72 x 4.72 x 2.76 [120 x 120 x 70]	56mm	PDF	1557DGASKET	\$4.50
1557DBK	1557DGY	\$11.25	4.72 x 4.72 x 1.77 [120 x 120 x 45]	31mm	PDF	1557DGASKET	\$4.50
1557FABK	1557FAGY	\$21.00	6.30 x 6.30 x 2.76 [160 x 160 x 70]	56mm	PDF	1557FGASKET	\$8.50
1557FBK	1557FGY	\$15.75	6.30 x 6.30 x 1.77 [160 x 160 x 45]	31mm	PDF	1557FGASKET	\$8.50
1557HABK	1557HAGY	\$22.00	7.87 x 7.87 x 2.76 [200 x 200 x 70]	56mm	PDF	1557HGASKET	\$8.75
1557HBK	1557HGY	\$21.00	7.87 x 7.87 x 1.77 [200 x 200 x 45]	31mm	PDF	1557HGASKET	\$8.75

Notes: Dimensions in inches [millimeters].

1557 Foot Kits



1554 Foot Kits					
Part Number Black	Price	Part Number Gray	Price	Description	Drawing Link
1557FOOT2BK-24	\$9.25	1557FOOT2GY-24	\$9.50	Polycarbonate foot mounting kit. For use with 1557xx2BK or 1557xx2GY enclosures. Includes (24) mounting feet and mounting hardware.	PDF
1557FOOTBK-24	\$8.75	1557FOOTGY-24	\$8.75	Polycarbonate foot mounting kit. For use with 1557xxBK or 1557xxGY enclosures. Includes (24) mounting feet and mounting hardware.	PDF