


NEMA 12 Multi-Door Freestanding



Applications

- Designed to house electrical, electronic, hydraulic or pneumatic controls and instruments.
- Provides some protection from falling dirt, dust, oil, and water.

Construction

- Formed 10-gauge steel.
- Smooth, continuously welded seams without knockouts, cutouts, or holes.
- Heavy duty body stiffeners are provided for extra rigidity.
- Reinforced eyebolts are provided for easy enclosure lifting.
- Double-door openings have gasketed overlapping doors, eliminating the need for a center post.
- Continuously hinged doors may be removed by pulling the hinge pin.
- Doors are secured with a 3-point padlocking handle.
- Latch rods are equipped with rollers for easier door closing.
- Oil-resistant gaskets are permanently secured.
- Removable 10-gauge subpanels are included in the enclosures.
- 3-door units have 2 panels (34 x 78 in [813 x 1930 mm] and 70 x 78 in [1727 x 1930 mm]).
- 4-door units have 2 panels (70 x 78 in [1727 x 1930 mm] each).
- Panel supports are provided in enclosures for easy subpanel installation.
- Collar studs are provided for mounting subpanels.
- A grounding stud is provided in the enclosure for each door, and a bonding stud is provided on the door.
- A literature pocket is provided for the inside of the door.

Finish

- Cover and enclosure are phosphatized and finished in recoatable smooth ANSI 61 gray powder coating.
- Removable subpanels are finished in RAL9003 white powder coating.

Listings

- UL 508A Type 12 [UL File E63523]
- CSA Type 12 [CSA File LR21001]
- Complies with
 - NEMA Type 12
 - IEC 60529, IP54



Shipping Schedule

| | |
|----------|-------------|
| Same day | 1 - 15 days |
|----------|-------------|

Color indicates shipping lead time in business days.

NEMA 12 Multi-Door Freestanding

| Part Number | Price | # of Doors | Enclosure Size HxWxD | Subpanel Dimensions H x W1 x W2 | Drawing Link |
|------------------|-------------|------------|--|---|---------------------|
| 1422MD3 | \$10,673.00 | 3 | 86.12 x 112.00 x 15.29 [2187 x 2845 x 388] | 78.00 x 34.00, 78.00 x 70.00 [1982 x 864, 1778] | PDF |
| 1422MD320 | \$11,014.00 | 3 | 86.12 x 112.00 x 21.29 [2187 x 2845 x 541] | 78.00 x 34.00, 78.00 x 70.00 [1982 x 864, 1778] | PDF |
| 1422MD4 | \$13,403.00 | 4 | 86.12 x 149.12 x 15.29 [2187 x 3788 x 388] | (2) 78.00 x 70.00 [1982 x 1778] | PDF |
| 1422MD420 | \$13,851.00 | 4 | 86.12 x 149.12 x 21.29 [2187 x 3788 x 541] | (2) 78.00 x 70.00 [1982 x 1778] | PDF |

Note: Dimensions in inches [millimeters].

NEMA 12 Multi-Door Freestanding



Dimensions

