

# NEMA 12 Multi-Door Freestanding



of the door.



## Applications

- Designed to house electrical, electronic, hydraulic or pneumatic controls and instruments.
- Provides some protection from falling dirt, dust, oil, and water.

## Construction

- Formed 10-gauge steel.
- Smooth, continuously welded seams without knockouts, cutouts, or holes.
- Heavy duty body stiffeners are provided for extra rigidity.
- Reinforced eyebolts are provided for easy enclosure lifting.
- Double-door openings have gasketed overlapping doors, eliminating the need for a center post.
- Continuously hinged doors may be removed by pulling the hinge pin.
- Doors are secured with a 3-point padlocking handle.
- Uses 1/4 turn latch handles.
- Latch rods are equipped with rollers for easier door closing.
- Oil-resistant gaskets are permanently secured.
- Removable 10-gauge subpanels are included in the enclosures.
- 3-door units have 2 panels (34 x 78 in [813 x 1930 mm] and 70 x 78 in [1727 x 1930 mm]).
- 4-door units have 2 panels (70 x 78 in [1727 x 1930 mm] each).
- Panel supports are provided in enclosures for easy subpanel installation.
- Collar studs are provided for mounting subpanels.
- A grounding stud is provided in the enclosure for each door, and a bonding stud is provided on the door.
- A literature pocket is provided for the inside

## Finish

- Cover and enclosure are phosphatized and finished in recoatable smooth ANSI 61 gray powder coating.
- Removable subpanels are finished in RAL9003 white powder coating.

## Listings

- UL 508A Type 12 [UL File E63523]
- CSA Type 12 [CSA File LR21001]
- Complies with
  - NEMA Type 12



## NEMA 12 Multi-Door Freestanding


Part Number	Price	# of Doors	Enclosure Size HxWxD	Subpanel Dimensions H x W1 x W2	Drawing Link
<a href="#">1422MD3</a>	\$8,782.00	3	86.12 x 112.00 x 15.29 [2187 x 2845 x 388]	78.00 x 34.00, 78.00 x 70.00 [1982 x 864, 1778]	<a href="#">PDF</a>
<a href="#">1422MD320</a>	\$9,034.00	3	86.12 x 112.00 x 21.29 [2187 x 2845 x 541]	78.00 x 34.00, 78.00 x 70.00 [1982 x 864, 1778]	<a href="#">PDF</a>
<a href="#">1422MD4</a>	\$10,799.00	4	86.12 x 149.12 x 15.29 [2187 x 3788 x 388]	(2) 78.00 x 70.00 [1982 x 1778]	<a href="#">PDF</a>
<a href="#">1422MD420</a>	\$11,128.00	4	86.12 x 149.12 x 21.29 [2187 x 3788 x 541]	(2) 78.00 x 70.00 [1982 x 1778]	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].

# NEMA 12 Multi-Door Freestanding



## Dimensions



# Enclosure Accessories

## Locks and Latches



### 1/4-Turn Latch Handles



#### Features

- Durable zinc diecast or stainless steel.
- Removable handle stop for clockwise / counter-clockwise operation.
- Textured powder coat Black finish on zinc cast handle.
- Maintains NEMA rating of enclosure.
- Padlock "trigger" design for security requirements.
- Optional key lock or defeater available. Key lock versions include two keys.

1/4-Turn Latch Handles							
Part Number	Price	Security Type	Latch Points	Material	Finish	For Use With These Hammond Enclosures Only	Drawing Link
<a href="#">MHK1</a>	\$127.00	padlocking	1	die-cast zinc	black matte	single-door NEMA 4 and NEMA 12	<a href="#">PDF</a>
<a href="#">MHKD1</a>	\$133.00	padlocking with defeater					<a href="#">PDF</a>
<a href="#">MHKL1</a>	\$144.00	combination keylocking/ padlocking					<a href="#">PDF</a>
<a href="#">MHK2</a>	\$217.00	padlocking	3	die-cast zinc	black matte	less than 60in (H) NEMA 4 and NEMA 12	<a href="#">PDF</a>
<a href="#">MHKD2</a>	\$228.00	padlocking with defeater					<a href="#">PDF</a>
<a href="#">MHKL2</a>	\$246.00	combination keylocking/ padlocking					<a href="#">PDF</a>
<a href="#">MHK3</a>	\$221.00	padlocking	3	die-cast zinc	black matte	60in (H) or greater NEMA 4 and NEMA 12	<a href="#">PDF</a>
<a href="#">MHKD3</a>	\$232.00	padlocking with defeater					<a href="#">PDF</a>
<a href="#">MHKL3</a>	\$251.00	combination keylocking/ padlocking					<a href="#">PDF</a>
<a href="#">MHK1SS</a>	\$195.00	padlocking	1	316 stainless steel	#4 brush	single-door NEMA 4X	<a href="#">PDF</a>
<a href="#">MHKD1SS</a>	\$215.00	padlocking with defeater					<a href="#">PDF</a>
<a href="#">MHKL1SS</a>	\$215.00	combination keylocking/ padlocking					<a href="#">PDF</a>
<a href="#">MHK2SS</a>	\$208.00	padlocking	3	316 stainless steel	#4 brush	less than 60in (H) NEMA 4X	<a href="#">PDF</a>
<a href="#">MHKD2SS</a>	\$229.00	padlocking with defeater					<a href="#">PDF</a>
<a href="#">MHKL2SS</a>	\$229.00	combination keylocking/ padlocking					<a href="#">PDF</a>
<a href="#">MHK3SS</a>	\$302.00	padlocking	3	316 stainless steel	#4 brush	60in (H) or greater NEMA 4X	<a href="#">PDF</a>
<a href="#">MHKD3SS</a>	\$332.00	padlocking with defeater					<a href="#">PDF</a>
<a href="#">MHKL3SS</a>	\$332.00	combination keylocking/ padlocking					<a href="#">PDF</a>