

NEMA 3, 4, and 12 Screw Cover Wall-Mount



Applications

Designed for use as a wiring box, junction box, terminal or pull box in indoor or outdoor applications where subject to windblown dust or rain.

Construction

- 14 gauge steel body up to 24in x 24in; 12 gauge body when 30in x 30in or larger
- 14 gauge steel cover up to 12in x 12in; 10 gauge cover when 16in x 16in or larger
- Smooth, continuously welded seams without knockouts, cutouts, or holes
- Captive stainless steel cover screws thread into sealed wells
- Seamless poured-in place gasket
- No provision for inner mounting panel
- Mounting Foot Kit sold separately - use [C3MTGFOOT](#)

Finish

- Enclosure and cover are finished with an ANSI 61 gray powder coating inside and outside

Listings

- UL 508A Listed; Type 3, 4, 12
- [File E65324]
- cULus Listed per CSA C22.2 No 94; Type 3, 4, 12
- Complies with
 - NEMA Type 3, 4 and 12
 - IEC 60529, IP66



NEMA 3, 4, and 12 Screw Cover Wall-Mount



NEMA 3, 4, and 12 Screw Cover Wall-Mount			
Part Number	Price	Enclosure Size HxWxD	Drawing Link
C3SC664GY	\$59.00	6.19 x 6.19 x 4.17 [157 x 157 x 106]	PDF
C3SC666GY	\$61.00	6.19 x 6.19 x 6.17 [157 x 157 x 157]	PDF
C3SC864GY	\$71.00	8.19 x 6.19 x 4.17 [208 x 157 x 106]	PDF
C3SC884GY	\$74.00	8.19 x 8.19 x 4.17 [208 x 208 x 106]	PDF
C3SC886GY	\$85.00	8.19 x 8.19 x 6.17 [208 x 208 x 157]	PDF
C3SC888GY	\$89.00	8.19 x 8.19 x 8.17 [208 x 208 x 208]	PDF
C3SC1084GY	\$87.00	10.19 x 8.19 x 4.17 [259 x 208 x 106]	PDF
C3SC10104GY	\$91.00	10.19 x 10.19 x 4.17 [259 x 259 x 106]	PDF
C3SC10106GY	\$94.00	10.19 x 10.19 x 6.17 [259 x 259 x 157]	PDF
C3SC12124GY	\$105.00	12.19 x 12.19 x 4.17 [310 x 310 x 106]	PDF
C3SC12106GY	\$101.00	12.19 x 10.19 x 6.17 [310 x 259 x 157]	PDF
C3SC12126GY	\$114.00	12.19 x 12.19 x 6.17 [310 x 310 x 157]	PDF
C3SC12128GY	\$117.00	12.19 x 12.19 x 8.17 [310 x 310 x 208]	PDF
C3SC16126GY	\$150.00	16.19 x 12.19 x 6.17 [411 x 310 x 157]	PDF
C3SC16166GY	\$153.00	16.19 x 16.19 x 6.23 [411 x 411 x 158]	PDF
C3SC16168GY	\$159.00	16.19 x 16.19 x 8.23 [411 x 411 x 209]	PDF
C3SC18186GY	\$170.00	18.19 x 18.19 x 6.23 [462 x 462 x 158]	PDF
C3SC20208GY	\$273.00	20.19 x 20.19 x 8.23 [513 x 513 x 209]	PDF
C3SC24208GY	\$300.00	24.19 x 20.19 x 8.23 [614 x 513 x 209]	PDF
C3SC24246GY	\$279.00	24.19 x 24.19 x 6.23 [614 x 614 x 158]	PDF
C3SC24248GY	\$328.00	24.19 x 24.19 x 8.23 [614 x 614 x 209]	PDF
C3SC242410GY	\$357.00	24.19 x 24.19 x 10.23 [614 x 614 x 260]	PDF
C3SC242412GY	\$375.00	24.19 x 24.19 x 12.23 [614 x 614 x 311]	PDF
C3SC303012GY	\$636.00	30.19 x 30.19 x 12.23 [767 x 767 x 311]	PDF
C3SC363612GY	\$706.00	36.19 x 36.19 x 12.23 [919 x 919 x 311]	PDF

Note: Dimensions in inches [millimeters].