

# NEMA 3, 4X, and 12 Screw Cover Wall-Mount



## Applications

Designed for use as a wiring box, junction box, terminal or pull box in indoor or outdoor applications where subject to hose down/precipitation or corrosion.

## Construction

- 14 gauge 304 stainless steel body up to 24in x 24in; 12 gauge body when 30in x 30in or larger
- 14 gauge 304 stainless steel cover up to 12in x 12in; 10 gauge cover when 16in x 16in or larger
- Smooth, continuously welded seams without knockouts, cutouts, or holes
- Captive stainless steel cover screws thread into sealed wells
- Seamless poured-in place gasket
- No provision for inner mounting panel
- Mounting Foot Kit sold separately — use [C4XMTGFOOT](#)

## Finish

- Enclosure and cover are unpainted, with a grained #4 finish.

## Listings

- UL 508A Listed; Type 3, 4X, 12
- [File E65324]
- cULus Listed per CSA C22.2 No 94; Type 3, 4X, 12
- Complies with
  - NEMA Type 3, 4X and 12
  - IEC 60529, IP66



NEMA 3, 4X, and 12 Screw Cover Wall-Mount			
Part Number	Price	Enclosure Size HxWxD	Drawing Link
<a href="#">C4XSC664SS</a>	\$154.00	6.13 x 6.19 x 4.17 [156 x 157 x 106]	<a href="#">PDF</a>
<a href="#">C4XSC666SS</a>	\$178.00	6.19 x 6.19 x 6.17 [157 x 157 x 157]	<a href="#">PDF</a>
<a href="#">C4XSC864SS</a>	\$175.00	8.19 x 6.19 x 4.17 [208 x 157 x 106]	<a href="#">PDF</a>
<a href="#">C4XSC884SS</a>	\$217.00	8.19 x 8.19 x 4.17 [208 x 208 x 106]	<a href="#">PDF</a>
<a href="#">C4XSC886SS</a>	\$229.00	8.19 x 8.19 x 6.17 [208 x 208 x 157]	<a href="#">PDF</a>
<a href="#">C4XSC1084SS</a>	\$248.00	10.19 x 8.19 x 4.17 [259 x 208 x 106]	<a href="#">PDF</a>
<a href="#">C4XSC10104SS</a>	\$266.00	10.19 x 10.19 x 4.17 [259 x 259 x 106]	<a href="#">PDF</a>
<a href="#">C4XSC10106SS</a>	\$299.00	10.19 x 10.19 x 6.17 [259 x 259 x 157]	<a href="#">PDF</a>
<a href="#">C4XSC12124SS</a>	\$362.00	12.19 x 12.19 x 4.17 [310 x 310 x 106]	<a href="#">PDF</a>
<a href="#">C4XSC12126SS</a>	\$387.00	12.19 x 12.19 x 6.17 [310 x 310 x 157]	<a href="#">PDF</a>
<a href="#">C4XSC12128SS</a>	\$401.00	12.19 x 12.19 x 8.17 [310 x 310 x 208]	<a href="#">PDF</a>
<a href="#">C4XSC16166SS</a>	\$445.00	16.19 x 16.19 x 6.23 [411 x 411 x 158]	<a href="#">PDF</a>
<a href="#">C4XSC16168SS</a>	\$493.00	16.19 x 16.19 x 8.23 [411 x 411 x 209]	<a href="#">PDF</a>
<a href="#">C4XSC18186SS</a>	\$541.00	18.19 x 18.19 x 6.23 [462 x 462 x 158]	<a href="#">PDF</a>
<a href="#">C4XSC24246SS</a>	\$595.00	24.19 x 24.19 x 6.23 [614 x 614 x 158]	<a href="#">PDF</a>
<a href="#">C4XSC24248SS</a>	\$709.00	24.19 x 24.19 x 8.23 [614 x 614 x 209]	<a href="#">PDF</a>
<a href="#">C4XSC242410SS</a>	\$914.00	24.19 x 24.19 x 10.23 [614 x 614 x 260]	<a href="#">PDF</a>
<a href="#">C4XSC242412SS</a>	\$1,098.00	24.19 x 24.19 x 12.23 [614 x 614 x 311]	<a href="#">PDF</a>
<a href="#">C4XSC303012SS</a>	\$1,394.00	30.19 x 30.19 x 12.23 [767 x 767 x 311]	<a href="#">PDF</a>
<a href="#">C4XSC363612SS</a>	\$1,694.00	36.19 x 36.19 x 12.23 [919 x 919 x 311]	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].