

NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Single-Door Freestanding with 3-Point Handle



Applications

- Designed to house electrical, electronic, hydraulic or pneumatic controls with provision for subpanel mounting or rack mounting of equipment.
- Provides protection where equipment may be hosed down or otherwise be very wet, or in specific applications where corrosion is a serious problem.
- A variety of subpanels, rack mounting rails and swing out frames are available to provide flexibility in mounting arrangements.

Construction

- Formed 12-gauge 304 stainless steel.
- Smooth, continuously welded seams without knockouts, cutouts, or holes.
- Heavy duty stainless steel lifting eyebolts are provided with reinforcing support angles.
- Doors are supported with heavy gauge continuous hinges.
- 3-point padlocking door handle.
- Seamless poured-in-place gasket.
- A grounding stud is provided in the enclosure, and a bonding stud is provided on the door.
- Mounting channels are welded on the inside of the enclosure for mounting of optional subpanels or rack equipment rails.

Finish

- Cover and enclosure are natural stainless steel with a #4 smooth brushed finish.
- Optional subpanels are finished in RAL9003 white powder paint.

Listings

- UL 508A Type 3R, 4, 4X, and 12 [UL File E65324]
- CSA Type 3R, 4, 4X, and 12 [CSA File LR21001]
- Complies with
 - NEMA Type 3R, 4, 4X, 12, and 13
 - IEC 60529, IP66

Shipping Schedule

Same day 1 - 15 days

Color indicates shipping lead time in business days.



NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Single-Door Freestanding with 3-Point Handle Front Access

304 Stainless Steel	Price	316 Stainless Steel	Price	Enclosure Size HxWxD	Optional Subpanels		Drawing Link
					Painted	Galvanized	
HN4FS602418SS	\$5,024.00	HN4FS602418S16	\$6,548.00	60.06 x 24.06 x 19.26 [1526 x 611 x 489]	60TWFW	60TWFWG	PDF
HN4FS603624SS	\$6,673.00	HN4FS603624S16	\$8,699.00	60.06 x 36.06 x 25.26 [1526 x 916 x 642]	60TYFW	60TYFWG	PDF
HN4FS722418SS	\$5,576.00	HN4FS722418S16	\$7,268.00	72.06 x 24.06 x 19.26 [1830 x 611 x 489]	72WFW	72WFWG	PDF
HN4FS722424SS	\$6,192.00	HN4FS722424S16	\$8,072.00	72.06 x 24.06 x 25.26 [1830 x 611 x 642]	72WFW	72WFWG	PDF
HN4FS723018SS	\$6,159.00	HN4FS723018S16	\$8,030.00	72.06 x 30.06 x 19.26 [1830 x 764 x 489]	72XFW	72XFWG	PDF
HN4FS723024SS	\$6,835.00	HN4FS723024S16	\$8,911.00	72.06 x 30.06 x 25.26 [1830 x 764 x 642]	72XFW	72XFWG	PDF
HN4FS723618SS	\$6,748.00	HN4FS723618S16	\$8,798.00	72.06 x 36.06 x 19.26 [1830 x 916 x 489]	72YFW	72YFWG	PDF
HN4FS723624SS	\$7,452.00	HN4FS723624S16	\$9,714.00	72.06 x 36.06 x 25.26 [1830 x 916 x 642]	72YFW	72YFWG	PDF
HN4FS723630SS	\$8,163.00	HN4FS723630S16	\$10,638.00	72.06 x 36.06 x 31.26 [1830 x 916 x 794]	72YFW	72YFWG	PDF
HN4FS723636SS	\$8,878.00	HN4FS723636S16	\$11,554.00	72.06 x 36.06 x 37.26 [1830 x 916 x 946]	72YFW	72YFWG	PDF
HN4FS902420SS	\$6,652.00	HN4FS902420S16	\$8,671.00	90.06 x 24.06 x 21.26 [2288 x 611 x 540]	90YFW	90YFWG	PDF
HN4FS903620SS	\$8,091.00	HN4FS903620S16	\$10,539.00	90.06 x 36.06 x 21.26 [2288 x 916 x 540]	90YFW	90YFWG	PDF
HN4FS903624SS	\$8,653.00	HN4FS903624S16	\$11,265.00	90.06 x 36.06 x 25.26 [2288 x 916 x 642]	90YFW	90YFWG	PDF
HN4FS903636SS	\$10,285.00	HN4FS903636S16	\$13,394.00	90.06 x 36.06 x 37.26 [2288 x 916 x 946]	90YFW	90YFWG	PDF

Note: Dimensions in inches [millimeters].

Table continued on next page

NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Single-Door Freestanding with 3-Point Handle



Shipping Schedule	
Same day	1 - 15 days

Color indicates shipping lead time in business days.

Table continued from previous page

NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Single-Door Freestanding with 3-Point Handle Dual Access							
304 Stainless	Price	316 Stainless	Price	Enclosure Size HxWxD	Optional Subpanels		Drawing Link
					Painted	Galvanized	
HN4FS722430DASS	\$7,982.00	HN4FS722430DS16	\$10,387.00	72.06 x 24.06 x 32.46 [1830 x 611 x 824]	72WFW	72WFWG	PDF
HN4FS722436DASS	\$8,725.00	HN4FS722436DS16	\$11,355.00	72.06 x 24.06 x 38.46 [1830 x 611 x 977]	72WFW	72WFWG	PDF
HN4FS722424DASS	\$7,247.00	HN4FS722424DS16	\$9,430.00	72.06 x 24.06 x 26.46 [1830 x 611 x 672]	72YFW	72YFWG	PDF
HN4FS723024DASS	\$7,982.00	HN4FS723024DS16	\$10,387.00	72.06 x 30.06 x 26.46 [1830 x 764 x 672]	72YFW	72YFWG	PDF
HN4FS723624DASS	\$8,725.00	HN4FS723624DS16	\$11,355.00	72.06 x 36.06 x 26.46 [1830 x 916 x 672]	72YFW	72YFWG	PDF
HN4FS723636DASS	\$10,365.00	HN4FS723636DS16	\$13,490.00	72.06 x 36.06 x 38.46 [1830 x 916 x 977]	72YFW	72YFWG	PDF
HN4FS903624DASS	\$10,108.00	HN4FS903624DS16	\$13,155.00	90.06 x 36.06 x 26.46 [2288 x 916 x 672]	90YFW	90YFWG	PDF
HN4FS903636DASS	\$12,014.00	HN4FS903636DS16	\$15,635.00	90.06 x 36.06 x 38.46 [2288 x 916 x 977]	90YFW	90YFWG	PDF

Note: Dimensions in inches [millimeters].

NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Single-Door Freestanding with 3-Point Handle



Dimensions

