

NEMA 3R Painted Galvanized Steel Screw Cover Wall-Mount



Applications

- Designed for use as a wiring/junction box.
- Provides protection against rain, sleet, snow and dripping water.

Construction

- Formed and spot welded from 16- or 14-gauge galvanized steel.
- Drip-shield top and seam-free sides, front and back.
- Slip-on removable cover fastened with plated steel screws.
- Embossed mounting holes on back of enclosure.
- Padlocking hasp.

Finish

- Enclosure and cover are finished in ANSI 61 gray powder coating.

Listings

- UL-50 Type 3R [UL File E65324]
- CSA Type 3R [CSA File LR21001]
- Complies with
 - NEMA Type 3R
 - IEC 60529, IP24



NEMA 3R Painted Galvanized Steel Screw Cover Wall-Mount			
Part Number	Price	Enclosure Size HxWxD	Drawing Link
C3R664SCNKO	\$23.50	6.12 x 6.49 x 4.28 [155 x 165 x 109]	PDF
C3R884SCNKO	\$33.00	8.12 x 8.49 x 4.28 [206 x 216 x 109]	PDF
C3R886SCNKO	\$37.00	8.12 x 8.49 x 6.28 [206 x 216 x 160]	PDF
C3R10104SCNKO	\$40.50	10.12 x 10.49 x 4.28 [257 x 266 x 109]	PDF
C3R10106SCNKO	\$47.00	10.12 x 10.49 x 6.28 [257 x 266 x 160]	PDF
C3R12124SCNKO	\$51.00	12.12 x 12.49 x 4.28 [308 x 317 x 109]	PDF
C3R12128SCNKO	\$77.00	12.12 x 12.49 x 8.28 [308 x 317 x 210]	PDF
C3R12126SCNKO	\$61.00	12.12 x 12.49 x 6.28 [308 x 317 x 160]	PDF
C3R16126SCNKO	\$88.00	16.12 x 12.49 x 6.28 [409 x 317 x 160]	PDF
C3R18186SCNKO	\$128.00	18.12 x 18.49 x 6.28 [460 x 470 x 160]	PDF
C3R18188SCNKO	\$162.00	18.12 x 18.49 x 8.28 [460 x 470 x 210]	PDF
C3R242410SCNKO	\$292.00	24.17 x 24.52 x 10.32 [614 x 623 x 262]	PDF
C3R242412SCNKO	\$269.00	24.17 x 24.52 x 12.32 [614 x 623 x 313]	PDF
C3R24246SCNKO	\$204.00	24.17 x 24.52 x 6.28 [614 x 623 x 160]	PDF
C3R24248SCNKO	\$223.00	24.17 x 24.52 x 8.28 [614 x 623 x 210]	PDF
C3R303012SCNKO	\$625.00	30.17 x 30.52 x 12.32 [766 x 775 x 313]	PDF
C3R363612SCNKO	\$735.00	36.17 x 36.52 x 12.32 [919 x 928 x 313]	PDF

Note: Dimensions in inches [millimeters].

NEMA 3R Painted Galvanized Steel Screw Cover Wall-Mount



Dimensions

