

NEMA 3R Wiring Trough



Application

- Designed for use to protect multiple wiring junctions in outdoor environments against the ingress of rain, sleet, snow and the external formation of ice.

Construction

- Formed and spot welded from 14 or 16-gauge galvanized steel.
- Drip shield top design protects the enclosure against rain, snow or sleet.
- Embossed mounting holes on back of enclosure.
- Slip on removable front cover is secured with screws.
- Padlocking hasp.
- To fully comply with UL870 - 2008 requirements a bonding stud is provided on the cover and a ground stud is provided in the enclosure.
- A #10 AWG - 12 in [305 mm] grounding strap with crimped on ring terminals is also provided to comply with UL requirements.

Finish

- Enclosure and cover are finished in ANSI 61 gray powder coating.

Listings

- UL 870 Type 3R [UL File E186830]
- CSA Type 3R [CSA File LL21312]
- Complies with
 - NEMA Type 3R
 - IEC 60529, IP24



Shipping Schedule

Same day	1 - 15 days
----------	-------------

Color indicates shipping lead time in business days.

NEMA 3R Wiring Trough			
Part Number	Price	Enclosure Size HxDxL	Drawing Link
C3RWT412	\$27.00	4.00 x 4.00 x 12.00 [102 x 102 x 305]	PDF
C3RWT418	\$41.00	4.00 x 4.00 x 18.00 [102 x 102 x 457]	PDF
C3RWT424	\$49.50	4.00 x 4.00 x 24.00 [102 x 102 x 610]	PDF
C3RWT436	\$71.00	4.00 x 4.00 x 36.00 [102 x 102 x 914]	PDF
C3RWT448	\$90.00	4.00 x 4.00 x 48.00 [102 x 102 x 1219]	PDF
C3RWT460	\$113.00	4.00 x 4.00 x 60.00 [102 x 102 x 1524]	PDF
C3RWT472	\$136.00	4.00 x 4.00 x 72.00 [102 x 102 x 1829]	PDF
C3RWT612	\$43.00	6.00 x 6.00 x 12.00 [152 x 152 x 305]	PDF
C3RWT624	\$67.00	6.00 x 6.00 x 24.00 [152 x 152 x 610]	PDF
C3RWT618	\$69.00	6.00 x 6.00 x 18.00 [152 x 152 x 457]	PDF
C3RWT636	\$92.00	6.00 x 6.00 x 36.00 [152 x 152 x 914]	PDF
C3RWT660	\$146.00	6.00 x 6.00 x 60.00 [152 x 152 x 1524]	PDF
C3RWT672	\$175.00	6.00 x 6.00 x 72.00 [152 x 152 x 1829]	PDF
C3RWT648	\$122.00	6.00 x 6.00 x 48.00 [152 x 152 x 1219]	PDF
C3RWT812	\$72.00	8.00 x 8.00 x 12.00 [203 x 203 x 305]	PDF
C3RWT824	\$112.00	8.00 x 8.00 x 24.00 [203 x 203 x 610]	PDF
C3RWT836	\$135.00	8.00 x 8.00 x 36.00 [203 x 203 x 914]	PDF
C3RWT848	\$174.00	8.00 x 8.00 x 48.00 [203 x 203 x 1219]	PDF

Note: Dimensions in inches [millimeters].

NEMA 3R Wiring Trough			
Part Number	Price	Enclosure Size HxDxL	Drawing Link
C3RWT860	\$203.00	8.00 x 8.00 x 60.00 [203 x 203 x 1524]	PDF
C3RWT872	\$232.00	8.00 x 8.00 x 72.00 [203 x 203 x 1829]	PDF
C3RWT896	\$315.00	8.00 x 8.00 x 96.00 [203 x 203 x 2438]	PDF
C3RWT8116	\$398.00	8.00 x 8.00 x 116.00 [203 x 203 x 2946]	PDF
C3RWT1024	\$179.00	10.00 x 10.00 x 24.00 [254 x 254 x 610]	PDF
C3RWT1036	\$202.00	10.00 x 10.00 x 36.00 [254 x 254 x 914]	PDF
C3RWT1048	\$227.00	10.00 x 10.00 x 48.00 [254 x 254 x 1219]	PDF
C3RWT1060	\$286.00	10.00 x 10.00 x 60.00 [254 x 254 x 1524]	PDF
C3RWT1072	\$323.00	10.00 x 10.00 x 72.00 [254 x 254 x 1829]	PDF
C3RWT1096	\$431.00	10.00 x 10.00 x 96.00 [254 x 254 x 2438]	PDF
C3RWT10116	\$538.00	10.00 x 10.00 x 116.00 [254 x 254 x 2946]	PDF
C3RWT1224	\$246.00	12.00 x 12.00 x 24.00 [305 x 305 x 610]	PDF
C3RWT1236	\$262.00	12.00 x 12.00 x 36.00 [305 x 305 x 914]	PDF
C3RWT1248	\$280.00	12.00 x 12.00 x 48.00 [305 x 305 x 1219]	PDF
C3RWT1260	\$321.00	12.00 x 12.00 x 60.00 [305 x 305 x 1524]	PDF
C3RWT1272	\$374.00	12.00 x 12.00 x 72.00 [305 x 305 x 1829]	PDF
C3RWT1284	\$436.00	12.00 x 12.00 x 84.00 [305 x 305 x 2134]	PDF
C3RWT1296	\$499.00	12.00 x 12.00 x 96.00 [305 x 305 x 2438]	PDF
C3RWT12116	\$629.00	12.00 x 12.00 x 116.00 [305 x 305 x 2946]	PDF

Note: Dimensions in inches [millimeters].