

# NEMA 1, 4, 4X, and 12 Stainless Steel Wiring Trough



## Finish

Troughs and covers are natural stainless steel with a smooth brushed finish.

## Listings

- UL 870 Type 1, 4, 4X, and 12 [File E186830]
- CSA Type 1, 4, 4X, and 12
- Complies with
  - NEMA Type 1, 4, 4X, and 12
  - IEC 60529, IP66



## Applications

Designed to enclose and protect multiple wiring junctions from dirt, dust, oil and water while providing a measure of corrosion protection.

## Construction

- Formed 14 gauge 304 stainless steel.
- Smooth continuously welded seams.
- Butt hinged cover is secured with easily operated screw clamps.
- Oil resistant gaskets are permanently secured.
- 12 gauge external mounting feet are welded to the back.

NEMA 1, 4, 4X, and 12 Wiring Trough			
Part Number	Price	Overall Size HxWxD	Drawing Link
<a href="#">1486B12SS</a>	\$331.00	2.50 x 2.50 x 12.00 [64 x 64 x 305]	<a href="#">PDF</a>
<a href="#">1486B18SS</a>	\$357.00	2.50 x 2.50 x 18.00 [64 x 64 x 457]	<a href="#">PDF</a>
<a href="#">1486B24SS</a>	\$384.00	2.50 x 2.50 x 24.00 [64 x 64 x 610]	<a href="#">PDF</a>
<a href="#">1486B36SS</a>	\$435.00	2.50 x 2.50 x 36.00 [64 x 64 x 914]	<a href="#">PDF</a>
<a href="#">1486B48SS</a>	\$488.00	2.50 x 2.50 x 48.00 [64 x 64 x 1219]	<a href="#">PDF</a>
<a href="#">1486B60SS</a>	\$538.00	2.50 x 2.50 x 60.00 [64 x 64 x 1524]	<a href="#">PDF</a>
<a href="#">1486B72SS</a>	\$585.00	2.50 x 2.50 x 72.00 [64 x 64 x 1829]	<a href="#">PDF</a>
<a href="#">1486C12SS</a>	\$387.00	4.00 x 4.00 x 12.00 [102 x 102 x 305]	<a href="#">PDF</a>
<a href="#">1486C18SS</a>	\$435.00	4.00 x 4.00 x 18.00 [102 x 102 x 457]	<a href="#">PDF</a>
<a href="#">1486C24SS</a>	\$485.00	4.00 x 4.00 x 24.00 [102 x 102 x 610]	<a href="#">PDF</a>
<a href="#">1486C30SS</a>	\$535.00	4.00 x 4.00 x 30.00 [102 x 102 x 762]	<a href="#">PDF</a>
<a href="#">1486C36SS</a>	\$579.00	4.00 x 4.00 x 36.00 [102 x 102 x 914]	<a href="#">PDF</a>
<a href="#">1486C48SS</a>	\$702.00	4.00 x 4.00 x 48.00 [102 x 102 x 1219]	<a href="#">PDF</a>
<a href="#">1486C60SS</a>	\$800.00	4.00 x 4.00 x 60.00 [102 x 102 x 1524]	<a href="#">PDF</a>
<a href="#">1486C72SS</a>	\$875.00	4.00 x 4.00 x 72.00 [102 x 102 x 1829]	<a href="#">PDF</a>
<a href="#">1486D12SS</a>	\$457.00	6.00 x 6.00 x 12.00 [152 x 152 x 305]	<a href="#">PDF</a>
<a href="#">1486D18SS</a>	\$529.00	6.00 x 6.00 x 18.00 [152 x 152 x 457]	<a href="#">PDF</a>
<a href="#">1486D24SS</a>	\$604.00	6.00 x 6.00 x 24.00 [152 x 152 x 610]	<a href="#">PDF</a>
<a href="#">1486D30SS</a>	\$674.00	6.00 x 6.00 x 30.00 [152 x 152 x 762]	<a href="#">PDF</a>
<a href="#">1486D36SS</a>	\$749.00	6.00 x 6.00 x 36.00 [152 x 152 x 914]	<a href="#">PDF</a>
<a href="#">1486D48SS</a>	\$894.00	6.00 x 6.00 x 48.00 [152 x 152 x 1219]	<a href="#">PDF</a>
<a href="#">1486D60SS</a>	\$1,075.00	6.00 x 6.00 x 60.00 [152 x 152 x 1524]	<a href="#">PDF</a>
<a href="#">1486D72SS</a>	\$1,226.00	6.00 x 6.00 x 72.00 [152 x 152 x 1829]	<a href="#">PDF</a>
<a href="#">1486E12SS</a>	\$562.00	8.00 x 8.00 x 12.00 [203 x 203 x 305]	<a href="#">PDF</a>
<a href="#">1486E24SS</a>	\$742.00	8.00 x 8.00 x 24.00 [203 x 203 x 610]	<a href="#">PDF</a>
<a href="#">1486E36SS</a>	\$947.00	8.00 x 8.00 x 36.00 [203 x 203 x 914]	<a href="#">PDF</a>
<a href="#">1486E48SS</a>	\$1,180.00	8.00 x 8.00 x 48.00 [203 x 203 x 1219]	<a href="#">PDF</a>
<a href="#">1486E60SS</a>	\$1,386.00	8.00 x 8.00 x 60.00 [203 x 203 x 1524]	<a href="#">PDF</a>
<a href="#">1486G24SS</a>	\$1,031.00	12.00 x 12.00 x 24.00 [305 x 305 x 610]	<a href="#">PDF</a>
<a href="#">1486G36SS</a>	\$1,327.00	12.00 x 12.00 x 36.00 [305 x 305 x 914]	<a href="#">PDF</a>
<a href="#">1486G48SS</a>	\$1,674.00	12.00 x 12.00 x 48.00 [305 x 305 x 1219]	<a href="#">PDF</a>
<a href="#">1486G60SS</a>	\$1,933.00	12.00 x 12.00 x 60.00 [305 x 305 x 1524]	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].

