

# Enclosure Accessories – Hole Seals and Plugs



## Hole Seals for Metal Enclosures

Designed to seal extra pushbutton holes, conduit openings, and knockout openings in metal enclosures from dirt, dust, oil and water. Conduit hole sizes are nominal trade sizes, not actual hole sizes. (Example: 1 in [25 mm] conduit actual diameter = 1.315in [33.4mm]).



### Shipping Schedule

Same day 1 - 5 days 1 - 7 days 1 - 15 days 1 - 20 days

Color indicates shipping lead time in business days.

<i>Steel Hole Seals with ANSI 61 Gray Polyester Powder</i>	<i>Price</i>	<i>Stainless Steel Hole Seals with Grained Finish</i>	<i>Price</i>	<i>Description</i>	<i>Hole Diameter</i>	<i>Wt. [lb]</i>
<b><u>WAS050</u></b>	\$6.25	<b><u>WAS050SS</u></b>	\$15.75	Wiegmann conduit hole seal, 0.5in [13mm], quick wing nut, oil-resistant gasket	0.87 [22]	0.1
<b><u>WAS075</u></b>	\$7.75	<b><u>WAS075SS</u></b>	\$21.50	Wiegmann conduit hole seal, 0.75in [19 mm], quick wing nut, oil-resistant gasket	1.14 [29]	
<b><u>WAS100</u></b>	\$10.75	<b><u>WAS100SS</u></b>	\$29.00	Wiegmann conduit hole seal, 1.00in [25mm], quick wing nut, oil-resistant gasket	1.38 [35]	
<b><u>WAS125</u></b>	\$13.00	<b><u>WAS125SS</u></b>	\$31.00	Wiegmann conduit hole seal, 1.25in [31.8mm], quick wing nut, oil-resistant gasket	1.61 [41]	0.2
<b><u>WAS150</u></b>	\$15.00	<b><u>WAS150SS</u></b>	\$34.50	Wiegmann conduit hole seal, 1.5in [38mm], quick wing nut, oil-resistant gasket	2.00 [51]	0.3
<b><u>WAS200</u></b>	\$16.50	<b><u>WAS200SS</u></b>	\$41.50	Wiegmann conduit hole seal, 2.00in [51mm], quick wing nut, oil-resistant gasket	2.52 [64]	
<b><u>WAS250</u></b>	\$19.50	—	—	Wiegmann conduit hole seal, 2.50in [64mm], quick wing nut, oil-resistant gasket	3.00 [76]	0.4
<b><u>WAS300</u></b>	\$25.50	—	—	Wiegmann conduit hole seal, 3.00in [76mm], quick wing nut, oil-resistant gasket	3.62 [92]	
<b><u>WAS350</u></b>	\$36.00	—	—	Wiegmann conduit hole seal, 3.50in [89mm], quick wing nut, oil-resistant gasket	4.13 [105]	
<b><u>WAS400</u></b>	\$46.00	—	—	Wiegmann conduit hole seal, 4.00in [102mm], quick wing nut, oil-resistant gasket	4.64 [118]	0.6
<b><u>WASPB</u></b>	\$8.50	<b><u>WASPBSS</u></b>	\$24.00	Wiegmann hole seal, for 30mm [1.18 in] pushbutton cutout, quick wing nut, oil-resistant gasket	1.18 [30]	0.1
<b><u>WASPBG</u></b>	\$6.25	<b><u>WASPBGSS</u></b>	\$15.75	Wiegmann hole seal, for 22mm [0.87 in] pushbutton cutout, quick wing nut, oil-resistant gasket	0.87 [22]	

Note: Dimensions in inches [millimeters].

# Enclosure Accessories – Hole Seals and Plugs



**AttaBox**  
A ROBROY ENCLOSURES™ BRAND

## Hole Plugs for Non-Metal Enclosures

Designed to seal extra pushbutton holes, conduit openings, and knockout openings in AttaBox fiberglass enclosures from dirt, dust, oil, and water. Conduit hole sizes are nominal trade sizes, not actual hole sizes. (Example: 1 in [25 mm] conduit actual diameter = 1.315in [33.4mm]).

### Shipping Schedule

Same day	1 - 5 days	1 - 7 days	1 - 15 days	1 - 20 days
----------	------------	------------	-------------	-------------

Color indicates shipping lead time in business days.



REHPSERIES1



REHPSERIES3



REHPSERIES8

### Hole Plugs for Non-Metal Enclosures

Hole Plugs	Price	Description	Nominal Hole Diameter Range	Wt [oz]
<a href="#"><u>REHPSERIES1</u></a>	\$5.25	AttaBox hole plug, fiberglass-reinforced polyester (FRP), closed-cell neoprene gasket, for 1/2 to 3/4-inch hole in non-metallic enclosure	0.50 - 0.81 [12.7 - 20.6]	2
<a href="#"><u>REHPSERIES1.5</u></a>	\$7.50	AttaBox hole plug, fiberglass-reinforced polyester (FRP), closed-cell neoprene gasket. For use with 1/2in conduit holes in non-metallic enclosures.	0.88 [22.4]	2
<a href="#"><u>REHPSERIES2</u></a>	\$6.25	AttaBox hole plug, fiberglass-reinforced polyester (FRP), closed-cell neoprene gasket, for 1/2- to 3/4-inch conduit holes and 22 or 30mm [1.18 in] pushbutton holes in non-metallic enclosure	0.88 - 1.28 [22.4 - 32.5]	2
<a href="#"><u>REHPSERIES3</u></a>	\$9.75	AttaBox hole plug, fiberglass-reinforced polyester (FRP), closed-cell neoprene gasket, for 1 to 1-1/4 inch conduit holes in non-metallic enclosure	1.38 - 1.75 [35.1 - 44.5]	2
<a href="#"><u>REHPSERIES4</u></a>	\$12.50	AttaBox hole plug, fiberglass-reinforced polyester (FRP), closed-cell neoprene gasket, for 1-1/2 to 2-inch conduit holes in non-metallic enclosure	2.00 - 2.56 [50.1 - 65.0]	2
<a href="#"><u>REHPSERIES5</u></a>	\$22.50	AttaBox hole plug, fiberglass-reinforced polyester (FRP), closed-cell neoprene gasket. For use with 2-1/2in conduit holes in non-metallic enclosures.	3.00 [76.2]	2
<a href="#"><u>REHPSERIES6</u></a>	\$30.50	AttaBox hole plug, fiberglass-reinforced polyester (FRP), closed-cell neoprene gasket. For use with 3in conduit holes in non-metallic enclosures.	3.62 [92.0]	2
<a href="#"><u>REHPSERIES7</u></a>	\$39.00	AttaBox hole plug, fiberglass-reinforced polyester (FRP), closed-cell neoprene gasket. For use with 3-1/2in conduit holes in non-metallic enclosures.	4.12 [104.7]	2
<a href="#"><u>REHPSERIES8</u></a>	\$50.00	AttaBox hole plug, fiberglass-reinforced polyester (FRP), closed-cell neoprene gasket. For use with 4in conduit holes in non-metallic enclosures.	4.62 [117.4]	2

Note: Dimensions in inches [millimeters].

## Agency Approvals

- Fiberglass hole plug for UL 1, 3R, 4, 4X, 6, 6P, 12 Industrial control panel enclosures. [UL File E64358]
- CSA 1, 12, 3, 3R, 4, 4X, 6, 6P:IEC Code IP66, IP67, IP68[CSA File LR069014]

