

Tools – Jobber Length Drill Bits

Jobber Length Drill Bits - Metric Sizes Continued									
Metric	Part # High Speed Steel	Pcs/Pkg	Price	Part # Cobalt 5	Pcs/Pkg	Price	Drill Size A (mm)	Flute Length B (mm)	Overall Length C (mm)
	214075	10	\$21.00	215075	10	\$45.50	7.5	69.0	109.0
	214080	10	\$25.50	215080	10	\$52.00	8.0	75.0	117.0
	214085	10	\$28.50	215085	10	\$63.00	8.5	75.0	117.0
	214090	10	\$31.00	215090	10	\$74.00	9.0	81.0	125.0
	214095	10	\$33.00	215095	10	\$76.00	9.5	81.0	125.0
	214100	10	\$39.00	215100	10	\$86.00	10.0	87.0	133.0
	214102	10	\$40.50	215102	10	\$93.00	10.2	87.0	133.0
	214105	5	\$21.00	215105	5	\$49.50	10.5	87.0	133.0
	214110	5	\$23.50	215110	5	\$51.00	11.0	94.0	142.0
	214115	5	\$26.00	215115	5	\$61.00	11.5	94.0	142.0
	214120	5	\$28.00	215120	5	\$63.00	12.0	101.0	151.0
	214125	5	\$29.50	215125	5	\$68.00	12.5	101.0	151.0
214130	5	\$36.00	215130	5	\$70.00	13.0	101.0	151.0	

Tools – Drill Bit Sets



Jobber length drill set
214214R0 shown

Drill Bit Sets		
Part #	Price	Description
101026USRO	\$69.00	Three-piece Step Drill Bit Set High Speed Steel, bright finish, spiral fluted with split point. Drill size 1: 6 steps from 3/16" to 1/2" with 1/16" increments. Shank size 1/4" Drill size 2: 13 steps from 1/8 to 1/2" with 1/32" increments. Shank size 1/4" Drill size 3: 9 steps from 1/4" to 3/4" with 1/16" increments. Shank size 3/8"
101026USERO	\$106.00	Three-piece Step Drill Bit Set HSS-Co5 spiral fluted with split point. Drill size 1: 6 steps from 3/16" to 1/2" with 1/16" increments. Shank size 1/4" Drill size 2: 13 steps from 1/8 to 1/2" with 1/32" increments. Shank size 1/4" Drill size 3: 9 steps from 1/4" to 3/4" with 1/16" increments. Shank size 3/8"
101026USTRO	\$111.00	Three-piece Step Drill Bit Set HSS-TiN coated spiral fluted with split point. Drill size 1: 6 steps from 3/16" to 1/2" with 1/16" increments. Shank size 1/4" Drill size 2: 13 steps from 1/8 to 1/2" with 1/32" increments. Shank size 1/4" Drill size 3: 9 steps from 1/4" to 3/4" with 1/16" increments. Shank size 3/8"
214214RO	\$55.00	19-piece jobber Length Drill Set Metric sizes 1.0 to 10.0 mm in increments of 0.5 mm High-speed steel, 118 degrees point
214215RO	\$65.00	25-piece jobber Length Drill Set Metric sizes 1.0 to 13.0 mm in increments of 0.5 mm High-speed steel, 118 degrees point
215214RO	\$106.00	19-piece jobber Length Drill Set Metric sizes 1.0 to 10.0 mm in increments of 0.5 mm High-speed steel Cobalt 5 alloy, 135 degrees point
215215RO	\$125.00	25-piece jobber Length Drill Set Metric sizes 1.0 to 13.0 mm in increments of 0.5 mm High-speed steel Cobalt 5 alloy, 135 degrees point
214850RO	\$38.00	21-piece jobber Length Drill Set Fractional sizes 1/16" to 3/8" in increments of 1/64" High-speed steel, 118 degrees point
214851RO	\$62.00	29-piece jobber Length Drill Set Fractional sizes 1/16" to 1/2" in increments of 1/64" High-speed steel, 118 degrees point.
215850RO	\$68.00	21-piece jobber Length Drill Set Fractional sizes 1/16" to 3/8" in increments of 1/64" High-speed steel Cobalt 5 alloy, 135 degrees point
215851RO	\$99.00	29-piece jobber Length Drill Set Fractional sizes 1/16" to 1/2" in increments of 1/64" High-speed steel Cobalt 5 alloy, 135 degrees point.
250850TRO	\$41.50	21-piece jobber Length Drill Set Fractional sizes 1/16" to 3/8" in increments of 1/64" TiN-coated high-speed steel, 118 degrees point
250851TRO	\$80.00	29-piece jobber Length Drill Set Fractional sizes 1/16" to 1/2" in increments of 1/64" TiN-coated high-speed steel, 118 degrees point