



Pliers & Cutting Tools

Alligator® Water Pump Pliers

The KNIPEX Alligator® water pump pliers take a fundamentally different approach to adjustable pliers: instead of a push-button or slide mechanism, the Alligator's® self-locking jaw geometry grips and holds under load without any manual locking step. Nine adjustment positions provide 30% more gripping capacity than standard designs, giving technicians more precise sizing on fittings, pipes, and fasteners from 7.3in to 10in tool length. For live electrical work, the 8808250SBA adds VDE 1000V-rated insulated multi-component handles, ASTM F1505-tested, without compromising the Alligator's core gripping performance. All models are chrome vanadium electric steel, forged and oil-hardened, DIN ISO 8976 compliant.

Features

- Self-locking jaw geometry grips without a separate locking step
- 9 adjustment positions for 30% more gripping capacity than standard designs
- Induction-hardened serrated gripping surface
- Pinch guard protects fingers and hands
- Chrome vanadium electric steel, forged and oil-hardened
- DIN ISO 8976 compliant
- 8808250SBA: VDE 1000V-rated insulated handles, ASTM F1505-tested



Alligator® Water Pump Pliers								
Part Number	Part Image	Overall Length	Jaw Length	Jaw Capacity	Jaw Thickness	Jaw Width	Insulated	Price
<u>8801180SBA</u>		7.3in [184mm]	0.85in [21.6mm]	1-1/2in round 1-27/64in hex	0.25in [6.3mm]	0.25in [6.3mm]	No	\$33.00
<u>8801250SBA</u>		10.0in [254mm]	1.28in [32.5mm]	2in round 1-13/16in hex	0.28in [7.2mm]	0.28in [7.2mm]	No	\$37.00
<u>8808250SBA*</u>		10.0in [254mm]	1.28in [32.5mm]	1-31/32in round 1-13/16in hex	0.28in [7.2mm]	0.28in [7.2mm]	Yes	\$56.00

* VDE 1000V-rated insulated handles, ASTM F1505-tested

Alligator® Water Pump Pliers Sets				
Part Number	Part Image	Number of Pieces	Set Includes	Price
<u>002007US1</u>		3	(3) Alligator adjustable pliers (7-1/4in, 10in, 12in), plastic tray with custom molded tool cavities	\$116.00